






REV.	ECN NO.	DESCRIPTION	DATE	DESIGN




SPECIFICATIONS

Current Rating: 3Amps
Insulation Resistance: 1000MΩ Min
Contact Resistance: 20mΩ Max
Withstanding Voltage: AC 1000V
Operation Temperature: -40°to+105°
Contact Material: Brass
Insrlator Material: Polyester(UL 94V-0)
Contact plating: Gold Flash
Standard: PBT
Max.Processing Temp: 200°C for30-60seconds
(220°C for5seconds)



RECOMMEND P.C.B LAYOUT
PCB TOLERANCE:±0.05 (TOP VIEW)

P/N	PIN	DIM.A	DIM.B
DC2.54-2*03PZ	2*3	5.08	26.92
DC2.54-2*04PZ	2*4	7.62	29.46
DC2.54-2*05PZ	2*5	10.16	32.00
DC2.54-2*06PZ	2*6	12.70	34.54
DC2.54-2*07PZ	2*7	15.24	37.08
DC2.54-2*08PZ	2*8	17.78	39.60
DC2.54-2*10PZ	2*10	22.86	44.70
DC2.54-2*12PZ	2*12	27.94	49.78
DC2.54-2*13PZ	2*13	30.48	52.30
DC2.54-2*15PZ	2*15	35.56	57.40
DC2.54-2*17PZ	2*17	40.64	62.50
DC2.54-2*20PZ	2*20	48.26	70.10
DC2.54-2*25PZ	2*25	60.96	82.85
DC2.54-2*30PZ	2*30	73.66	95.40
DC2.54-2*32PZ	2*32	78.74	100.48

TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd				
X.±0.30	X.°±5°	PART NO. DC2.54-2*NPZ	TITLE: 2.54DC2-NPin H17 180度 PC3.8 PBT			
X.X±0.25	X.X°±1°					
X.XX±0.20	X.XX°±0.5°					
UNITS	mm	DESIGN: Ethan	MANUFACTURE DWG			
MATERILA	— — —	CHED: Olvia				
FINISH	— — —	APPD: Ava		SCALE	SHEET	
					N:A	1/1