










NOTE:
IP67 waterproof

PIN NO	A1&B12	A4&B9	A5	A5	A9&B4	A12&B1
SIGNAL NAME	GND	VBUS	CC1	CC2	VBUS	GND
PCB PAD NO.	C1	C2	C3	C4	C5	C6



对插示意图



RECOMMENDED P.C.B. LAYOUT
TOLERANCE UNSPECIFIED ±0.05mm

NO.	PART NAME	MATERIAL	QTY	FINISHING	TOLERANCE UNLESS SPECIFIED									
5	SHELL	STEEL	1	NI-Plated	UP TO 5mm: ±0.1	ANGULAR ±1°	1	NO	DATE	REVISIONS		BY	APPD	
4	SHIELDING PLATE	STEEL	1	NI-Plated	ABOVE 5mm: ±0.2					UNIT : MM	ROHS COMPLIANT	DWN		
3	CONTACT	PBS	6	SN/Au/NI-Plated						SCALE: 1:1	CHK'D			
2	SHELL HOUSING	LCP	1	BLACK							APPD			
1	HOUSING	LCP	1	BLACK										
<p>TITLE: USB JACK MODEL: USB-312FSB-B-SU</p>										<p>HAOYU(HONGKONG)LIMITED 皓宇(香港)有限公司</p>			<p>PRO.AGL: </p>	<p>REV :A0</p>