






1	2	3	4	5	6	7	8					
A	性能指标(Electrical)			材质与表面处理(Materials & Plating)								
	1.特性阻抗(Impedance) : 50		序号(Serial)	零件名称(Part Name)		材质(Material)						
	2.频率范围(Frequency) : DC-6GHz			1	壳体(Body)	黄铜(Brass)	镀金(Gold Plated)					
	3.工作电压(Working Voltage) : 335V(Volts Max)		3	2	绝缘子(Insulator)	聚四氟乙烯(PTFE)						
	4.介质耐压(Dielectric Withstanding Voltage) : 1000V(Volts)			3	中心孔针(Contact Pin)	黄铜(Brass)	镀金(Gold Plated)					
	5.工作温度(Insulation Resistance) : -65 ~+165		4	4	壳体(Body)	黄铜(Brass)	镀金(Gold Plated)					
	6.无铅, 符合RoHS标准(Lead Free, RoHS Compliant)			5	绝缘子(Insulator)	聚四氟乙烯(PTFE)						
B												
C												
D	 											
零件 代号	RECOMMENDED PCB LAYOUT											
借(通)用件登记	RECOMMENDED MOUNTING HOLE											
描图												
描校												
旧底图总号												
底图总号												
签字												
日期												
1	2	3	4	5	6	7	8					

标记	处数	分区	更改文件号	签名	年月日	阶段	标记	重量	比例	RF2-49B-T-00-50-G-HDW-02
设计			标准化							
校核			工艺							
主管设计			审核							
			批准			共1张	第1张	版本		未标注公差的, 以下列公差表为准
										.X ± 2.55 .XX ± 0.51 .XXX ± 0.38
										.XX ± 0.38 .XXX ± 0.26