





	1	2	3	4	5	6
	ROHS Compliant	序号	品名	材质		
A		1	0.5掀盖立式胶芯(H=5.4)	LCP UL94V-0 本色		
		2	0.5掀盖立式后盖(H=5.4)	LCP UL94V-0 黑色		
		3	0.5掀盖立式端子(H=5.4)	铜合金/表面镀金		
D		4	0.5掀盖立式焊片(H=5.4)	铜合金/表面镀锡		






F	P/N	PIN	DIM A	DIM B	DIM C	DIM D	DIM E	DIM F
	FPC-0.5FZ-5PLBR-H54	5	2.00	3.06	6.00	4.40	2.50	4.00
	FPC-0.5FZ-6PLBR-H54	6	2.50	3.56	6.50	4.90	3.00	4.50
	FPC-0.5FZ-7PLBR-H54	7	3.00	4.06	7.00	5.40	3.00	5.00
G	FPC-0.5FZ-8PLBR-H54	8	3.50	4.56	7.50	5.90	4.00	5.50
	FPC-0.5FZ-9PLBR-H54	9	4.00	5.06	8.00	6.40	4.00	6.00
	FPC-0.5FZ-10PLBR-H54	10	4.50	5.56	8.50	6.90	4.00	6.50
	FPC-0.5FZ-11PLBR-H54	11	5.00	6.06	9.00	7.40	4.00	7.00
H	FPC-0.5FZ-12PLBR-H54	12	5.50	6.56	9.50	7.90	4.00	7.50
	FPC-0.5FZ-13PLBR-H54	13	6.00	7.06	10.00	8.40	4.00	8.00
	FPC-0.5FZ-14PLBR-H54	14	6.50	7.56	10.50	8.90	4.00	8.50
	FPC-0.5FZ-15PLBR-H54	15	7.00	8.06	11.00	9.40	4.00	9.00
I	FPC-0.5FZ-16PLBR-H54	16	7.50	8.56	11.50	9.90	4.00	9.50
								
	FPC-0.5FZ-56PLBR-H54	56	27.50	28.56	31.50	29.90	8.00	29.50
	FPC-0.5FZ-57PLBR-H54	57	28.00	29.06	32.00	30.40	8.00	30.00
J	FPC-0.5FZ-58PLBR-H54	58	28.50	29.56	32.50	30.90	8.00	30.50
	FPC-0.5FZ-59PLBR-H54	59	29.00	30.06	33.00	31.40	8.00	31.00
	FPC-0.5FZ-60PLBR-H54	60	29.50	30.56	33.50	31.90	8.00	31.50



技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: -25°C~85°C.
3. 额定电流: 0.5A
4. 额定电压: 50V, AC.
5. 接触电阻: ≤50mΩ MAX.
6. 绝缘电阻: ≥500MΩ Min.
7. 耐电压: 150V AC/1Minute

12	13	14	15
MAPX	MODIFICATION	DATE	DRAW



MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES		TITLE: 0.5 Pitch 立式正脚(H=5.4)业务图	
DECIMALS:	ANGLES:	PAR	FPC-0.5FZ-NPLBR-H54
X.:±0.50	±1°	DWN	Lucas
.X:±0.20		CHKD	Ethan
.XX:±0.10		APVD	Jacob
.XXX:±0.05		SCALE:1:1	UNIT:MM
CUSTOMER COPY		SIZE:A4	SHEET:1F1
			REV:A