






NOTES:

1.MECHANICAL:MATING FORCE: 5-20N .
UNMATING FORCE: 8-20N .
DURABILITY: 10000 CYCLES MIN.



2.ELECTRICAL:
CURRENT: 5.0A MAX
VOLTAGE: 20V MAX
WITHSTANDING VOLTAGE: 100V AC
CONTACT RESISTANCE: 40 mΩ MAX INITIAL;
50 mΩ MAX AFTER 10000 CYCLES

3.ENVIRONMENTAL:
OPERATING TEMPERATURE RANGE -30°C ~ +80°C



4.Salt Spray:24H



A1	GND	B12	GND
A2	—	B11	—
A3	—	B10	—
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	DP1	B7	DN2
A7	DN1	B6	DP2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A10	—	B3	—
A11	—	B2	—
A12	GND	B1	GND



BOM			
名称	材料规格		
主体	LCP 黑色 端子C2680 T=0.15mm 全金1u” 卡勾:SUS301 H T=0.15mm 素材		
外壳	SUS201 1/4H T=0.30mm 亮Ni:80u”		
MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES		 TITLE:Type-C 16Pin 板上型 L=8.35	
DECIMALS:	ANGLES:	PAR	TYPEC-304D-BCP16L835
X.:±0.50	X.':±5°	DWN	Lucas
X.X:±0.35	X.X':±3°	CHKD	Ethan
X.XX:±0.25	X.XX':±2.5°	APVD	Jacob
CUSTOMER COPY		SCALE1:1	UNIT:MM
		SIZE:A4	SHEET:1F2
			REV:A



10卷/每箱

MANUFACTURE DWG		东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd		
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE:Type-C 16Pin 板上型 L=8.35	
			PAR	TYPEC-304D-BCP16L835
DECIMALS:	ANGLES:		DWN	Lucas
X.:±0.50	X.'':±5°		CHKD	Ethan
X.X:±0.35	X.X':±3°		APVD	Jacob
X.XX:±0.25	X.XX':±2.5°	CUSTOMER COPY	SCALE1:1	UNIT:MM
			SIZE:A4	SHEET:2F2
				REV:A