


	1	2	3	4	5	6	7	8					
A	HL-SMA-IPEX-JJ-02				材质与表面处理(Materials & Plating)								
B					序号(Serial)	零件名称(Part Name)	材质(Material)	表面处理(Plating)					
					1	螺套(Screw Sleeve)	黄铜(Brass)	镀金(Gold Plated)					
					2	绝缘子(Insulator)	聚四氟乙烯(PTFE)						
					3	中心针(Contact Pin)	黄铜(Brass)	镀金(Gold Plated)					
					4	密封圈(Sealing Ring)	硅橡胶(Silicone Rubber)						
					5	卡环(Circlip)	磷青铜(Beryllium Copper)						
C					6	外壳(Body)	黄铜(Brass)	镀金(Gold Plated)					
					性能指标(Electrical)								
					1.特性阻抗(Impedence)：50Ω								
					2.频率范围(Frequency)：DC-6GHz								
					3.接触电阻：内导体(Center Contact Resistance)≤3mΩ 外导体(Outer Contact Resistance)≤2mΩ								
					4.绝缘阻抗(Insulation Resistance)：≥5000MΩ								
D					5.介质耐压(Dielectric Withstanding Voltage)：1000V(Volts RMS)								
					6.驻波比(VSWR)：≤1.25								
													
				成都恒利泰科技有限公司 Chengdu HenryTech Technology co., Ltd									
				标记	处数	分区	更改文件号	签名	年月日	阶段标记	重量	比例	HL-SMA-IPEX-JJ-02
				设计			标准化						
				校核			工艺						
				主管设计			审核						
							批准			共1张	第1张	版本	
	1	2	3	4	5	6	7	8					