

RoHS

Specifications(规格):


- 1.Impedance(特性阻抗): 50Ω;
2.Frequency (工作频率): DC~6GHz;
3.VSWR (电压驻波比): 1.50@3GHz; 1.60@6GHz; .
4.Insulation resistance(绝缘阻抗): ≥100MΩ;
5.Dielectric withstand voltage (介质耐电压): 800V AC;
6.Mating cycles (耐久性): ≥25 cycles;
7.Retention force latch(保持力): ≥110N;
8.Temperature range(使用温度): -40℃~+105℃;

PART NO.:


X Z X R X - M4M-XXXX-M4M- X X
① ② ③ ④ ⑤

- ① Cable TYPE:
3: RG174
4: 1.5DS
7: Dacar302
8: RG174LL
② Successive number: 1~Z
③ Length (mm): 1000=1000mm
④ Coding A: A~Z
⑤ Coding B (B1~B4): A~Z

接点表(Wiring Table)



REVISIONS				
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE
A0	N/A		INITIAL RELEASE	2024.10.28



PART NO.	Length (mm/inch)	TOLERANCES (mm/inch)
XZ8R1-M4F-1000-M4M-XX	1000 [39.370]	±15 [0.591]
XZ8R1-M4F-1500-M4M-XX	1500 [59.055]	±15 [0.591]
XZ8R1-M4F-2000-M4M-XX	2000 [78.740]	±20 [0.787]
XZ8R1-M4F-3000-M4M-XX	3000 [118.110]	±30 [1.181]

3	Connector	MINI FAKRA Male connector(R),Z Code	1SET	
2	Connector	MINI FAKRA Female connector(R),Z Code	1SET	
1	Cable	RG174LL Cable PVC OD2.80mm Black,-40~105℃	4PCS	
NO.	NAME	SPEC.	Q'TY	NOTE



XKB INDUSTRIAL PRECISION CO.,LIMITED

DESIGN	希文	VIEW:	MODEL TYPE: Assembly cable, MINI FAKRA series
CHECKED		UNIT: mm/in	PART NO.: XZ8R1-M4F-XXXX-M4M-ZZ
APPROVED		SIZE: A4	DWG NO.: X-XZ8R1-M4F-XXXX-M4M-ZZ
			SCALE: N/A
			PAGE: 1/1
			REVISION: A0