

RoHS

Specifications(规格):


- 1.Impedance(特性阻抗) : 50Ω;
2.Frequency (工作频率): DC~6GHz;
3.VSWR (电压驻波比): 1.60 Max.
4.Insulation resistance(绝缘阻抗): ≥100MΩ;
5.Dielectric withstand voltage (介质耐电压): 800V AC;
6.Mating cycles (耐久性): ≥25 cycles;
7.Retention force latch(保持力): ≥110N;
8.Temperature range(使用温度): -40℃~+105℃;

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN


PART NO.:

X Z X R X - M2F-XXXX-K1F- X X
① ② ③ ④ ⑤

- ① Cable TYPE:
3: RG174
4: 1.5DS
7: Dacar302/RTK031
8: RG174LL
② Successive number: 1~Z
③ Length (mm): 1000=1000mm
④ Coding A: A~Z
⑤ Coding B: A~Z



接点表(Wiring Table)



PART NO.	Length (mm/inch)	TOLERANCES (mm/inch)
XZ7RH-M2F-500-K1F-ZZ	500 [19.685]	±10 [0.394]
XZ7RH-M2F-1000-K1F-ZZ	1000 [39.370]	±15 [0.591]
XZ7RH-M2F-2000-K1F-ZZ	2000 [78.740]	±20 [0.787]
XZ7RH-M2F-3000-K1F-ZZ	3000 [118.110]	±30 [1.181]
XZ7RH-M2F-4000-K1F-ZZ	4000 [157.480]	±60 [2.362]

3	Connector	FAKRA Female connector,Z Code	2SET	
2	Connector	Horizontal Double MINI FAKRA Female Connector,Z Code	1SET	R版
1	Cable	RTK031 Cable PVC OD3.30 Black,-40~105℃	2PCS	
NO.	NAME	SPEC.	Q'TY	NOTE

	DESIGN	希文	VIEW: 	MODEL TYPE: Assembly cable, Horizontal,Double MINI FAKRA series
	CHECKED		UNIT: mm/in	PART NO.: XZ7RH-M2F-XXXX-K1F-ZZ
	APPROVED		SIZE: A4	DWG NO.: X-XZ7RH-M2F-XXXX-K1F-ZZ
XKB INDUSTRIAL PRECISION CO.,LIMITED				SCALE: N/A
				PAGE: 1/1
				REVISION: A0