

RoHS

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2024.10.28	


Specifications(规格):

- 1.Impedance(特性阻抗): 50Ω;
2.Frequency (工作频率): DC~6GHz;
3.VSWR (电压驻波比): 1.50@3GHz; 1.60@6GHz;
4.Insulation resistance(绝缘阻抗): ≥100MΩ;
5.Dielectric withstand voltage (介质耐电压): 800V AC;
6.Mating cycles (耐久性): ≥25 cycles;
7.Engagement force(啮合力): ≤ 25N;
8.Retention force latch(保持力): ≥110N;
9.Temperature range(使用温度):
-40℃~+105℃;


PART NO.:

XZ X X -K1M- XXXX -K1M- X X
① ② ③ ④ ⑤

- ① Cable TYPE:
3: RG174
4: 1.5DS
6: RG58
7: Dacar302
8: RG174LL
9: RG58LL
② Successive number: 1~Z
③ Length (mm): 1000=1000mm
④ Coding A: A~Z
⑤ Coding B: A~Z



接点表(Wiring Table)



2	Connector	FAKRA Male connector,Z Code	2SET	
1	Cable	RG58LL Cable PVC OD5.0mm Black,-40~105℃	1PCS	
NO.	NAME	SPEC.	Q'TY	NOTE

www.helloxkb.com www.helloxkb.cn www.xk-dg.cn



XKB INDUSTRIAL PRECISION CO.,LIMITED

DESIGN	希文	VIEW:	MODEL TYPE: Assembly cable, FAKRA series
CHECKED		UNIT: mm/in	PART NO.: XZ91-K1M-5000-K1M-ZZ
APPROVED		SIZE: A4	DWG NO.: X-XZ91-K1M-5000-K1M-ZZ

SCALE	PAGE	REVISION
N/A	1/1	A0