









SUGGESTED PCB LAYOUT
(COMPONENT SIDE)



REV.	DESCRIPTION	DATE
A/0	初版发行	2016.11.28
B/0	升 B 版	2024.8.12

技术参数:

- 1、所有材料符合ROHS2.0/REACH/HF要求。
- 2、额定电流: 2A, AC, DC;
- 3、额定电压: 100V, AC, DC;
- 4、温度范围: -25℃~+85℃;
- 5、接触电阻: $\leq 0.02\Omega$;
- 6、绝缘电阻: $\geq 1000M\Omega$;
- 7、耐压: 800V, AC/minute.
- 8、产品料号:

A10001 - n AB - 03 T1

孔位

产品类型

AB:立贴针座

电镀

T1:镀亮锡

胶芯材质

03:LCP 本色

Circuits	Dimensions (mm)			
	A	B	C	D
02	2.00	1.00	8.00	4.80
03	4.00	2.00	10.00	6.80
04	6.00	4.00	12.00	8.80
05	8.00	6.00	14.00	10.80
06	10.00	8.00	16.00	12.80
07	12.00	10.00	18.00	14.80
08	14.00	12.00	20.00	16.80
09	16.00	14.00	22.00	18.80
10	18.00	16.00	24.00	20.80
11	20.00	18.00	26.00	22.80
12	22.00	20.00	28.00	24.80
13	24.00	22.00	30.00	26.80
...	...	...	...	...
20	38.00	36.00	44.00	40.80

4	吸盖 Cap	LCP (UL94V-0)	1	本色
3	焊片 Fitting Nail	黄铜 Brass	2	电镀(锡): 整个表面镀底镍30u"MIN, 再镀锡80u". MIN.
2	端子 Contact	黄铜 Brass	n*1	电镀(锡): 整个表面镀底镍30u"MIN, 再镀锡80u". MIN.
1	基座 Wafer	LCP (UL94V-0)	1	本色
序号	名称	材料	数量	附注

GENERAL TOLERANCES				浙江深海电子有限公司	
0.X	±0.25	X.°	±3°		
0.XX	±0.12			SHEET	PROD. NAME SH-PH2.0-NALT
0.XXX	±0.05	X.X°	±0.5°	1 OF 1	PART NO. A20001-nAB-03T1
UNIT	SIZE	SCALE		DRAWING NO. H20005-00	
MM	A4	1:1		TITLE 2.0mm pitch 180° WAFER-SMT TYPE	