





REV.	DESCRIPTION	DATE
A/0	新版发行	
B/0	升B版	2024.7.11



技术参数:

- 1、所有材料符合ROHS2.0/REACH/HF要求。
- 2、额定电流: 1A, AC, DC;
- 3、额定电压: 50V, AC, DC;
- 4、温度范围: -25℃~+85℃;
- 5、接触电阻: $\leq 0.02\Omega$;
- 6、绝缘电阻: $\geq 100M\Omega$;
- 7、耐压: 500V, AC/minute.
- 8、适用线规: AWG#32 to #28
- 9、产品料号:

A10001 - n AB - 03 T1
孔位
产品类型
AB: 立贴针座
电镀
T1: 镀亮锡
胶芯材质
03: LCP

Circuits	Dimensions (mm)		
	A	B	C
02	1.00	4.30	2.40
03	2.00	5.30	3.40
04	3.00	6.30	4.40
05	4.00	7.30	5.40
06	5.00	8.30	6.40
07	6.00	9.30	7.40
08	7.00	10.30	8.40
09	8.00	11.30	9.40
10	9.00	12.30	10.40
11	10.00	13.30	11.40
12	11.00	14.30	12.40
13	12.00	15.30	13.40
14	13.00	16.30	14.40
15	14.00	17.30	15.40
16	15.00	18.30	16.40
17	16.00	19.30	17.40
18	17.00	20.30	18.40
19	18.00	21.30	19.40
20	19.00	22.30	20.40

4	吸盘 CAP	LCP (UL94V-0)	1	本色
3	焊片 Fitting Nail	磷青铜 Phosphor Bronze	2	电镀(锡): 整个表面镀底锡30u"MIN, 再镀锡 80u"MIN.
2	端子 Contact	磷青铜 Phosphor Bronze	n*1	电镀(锡): 整个表面镀底锡30u"MIN, 再镀锡 80u"MIN.
1	基座 Wafer	LCP (UL94V-0)	1	本色
序号	名称	材料	数量	附注

GENERAL TOLERANCES				DRAWN BY 刘焕刚/2024.7.11		浙江深海电子有限公司	
0.X	±0.25	X.°	±3°	CHK. BY 朱江浩/2024.7.11			
0.XX	±0.12			APRV. BY 姚婷/2024.7.11			
0.XXX	±0.05	X.X°	±0.5°			SHEET 1 OF 1	PROD. NAME SH-SH1.0-NALT
UNIT	SIZE	SCALE		DRAWING NO. H10001-00		PART NO. A10001-nAB-03T1	
MM	A4	1:1				TITLE 1.0mm pitch 180° WAFER-SMT TYPE	

借用登记

旧底图总号

底图总号

签字

日期