




REV.	DESCRIPTION	DATE
A/0	新版发行	2022.11.28
B/0	升 B 版	2024.8.14

- 技术参数:
- 1、所有材料符合ROHS2.0/REACH要求。
 - 2、额定电流: 2A, AC, DC;
 - 3、额定电压: 250V, AC, DC;
 - 4、温度范围: -25℃~+85℃;
 - 5、接触电阻: ≤0.03Ω;
 - 6、绝缘电阻: ≥1000MΩ;
 - 7、耐压: 1000V, AC/minute.
 - 8、产品料号:

A20002 - n A - 01 T1
孔位 ———— A ———— T1
产品类型 ————
A:直插针座
电镀
T1:镀亮锡
胶芯材质
01:PA66白色

Circuits	Dimensions (mm)		
	A	B	C
02	2.00	6.00	3.00
03	4.00	8.00	3.30
04	6.00	10.00	4.00
05	8.00	12.00	6.00
06	10.00	14.00	8.00
07	12.00	16.00	10.00
08	14.00	18.00	12.00
09	16.00	20.00	14.00
10	18.00	22.00	16.00
11	20.00	24.00	18.00
12	22.00	26.00	20.00
13	24.00	28.00	22.00
14	26.00	30.00	24.00
15	28.00	32.00	26.00

2	端子 Contact	黄铜	n x 1	电镀(铜): 整个表面镀层30u"MIN, 再镀银 80u"MIN.
1	基座 Wafer	PA66	1	纯
序号	名称	材料	数量	附注

GENERAL TOLERANCES				DRAWN BY	浙江深海电子有限公司			
0.X ±0.25 X.° ±3°				CHK. BY				
0.XX ±0.12								
0.XXX ±0.05 X.X° ±0.5°				APRV. BY				
					SHEET	PROD. NAME SH-HY2.0-NP		
UNIT	SIZE	SCALE		DRAWING NO.		1 OF 1	PART NO. A20002-nA-01T1	
				H20007-00		TITLE 2.0mm pitch 180° WAFER-DIP TYPE		
MM	A4	1:1						

SUGGESTED PCB LAYOUT
(COMPONENT SIDE)