





REV.	DESCRIPTION	DATE
A/0	新版发行	2013.10.13
B/0	升 B 版	2024.8.14



2PIN 外观

技术参数:

- 所有材料符合ROHS2.0/REACH/HF要求。
- 额定电流: 3A, AC, DC;
- 额定电压: 250V, AC, DC;
- 温度范围: -25°C ~ +85°C;
- 接触电阻: ≤ 0.02 Ω;
- 绝缘电阻: ≥ 1000MΩ;
- 耐压: 1000V, AC/minute.
- 产品料号:

A25001 - n AB - 03 T1
孔位
产品类型
AB: 立贴针座
电镀
T1: 镀亮锡
胶芯材质
03: LCP 本色

Circuits	Dimensions (mm)		
	A	B	C
02	2.50	5.90	10.00
03	5.00	8.40	12.50
04	7.50	10.90	15.00
05	10.00	13.40	17.50
06	12.50	15.90	20.00
07	15.00	18.40	22.50
08	17.50	20.90	25.00
09	20.00	23.40	27.50
10	22.50	25.90	30.00
11	25.00	28.40	32.50
12	27.50	30.90	35.00
13	30.00	33.40	37.50
14	32.50	35.90	40.00
15	35.00	38.40	42.50
16	37.50	40.90	45.00

4	覆蓋 Cap	LCP (UL94V-0)	1	壳
3	焊片 fitting	黄铜	2	电镀(锡): 整个表面镀锡30μ"MIN, 再镀锡 80μ"MIN..
2	端子 Contact	黄铜	n×1	电镀(锡): 整个表面镀锡30μ"MIN, 再镀锡 80μ"MIN..
1	基座 Wafer	LCP (UL94V-0)	1	壳

序号	名 称	材 料	数 量	附 注

GENERAL TOLERANCES			DRAWN BY 罗美程/2024.8.17	浙江深海电子有限公司	
0.X ± 0.25 X.° ± 3°			CHK. BY 朱江浩/2024.8.17		
0.XX ± 0.12			APRV. BY 姚 娟/2024.8.17		
UNIT	SIZE	SCALE		DRAWING NO.	SHEET PROD. NAME SH-XH2.54-NALT
MM	A4	1:1		H25001-00	1 OF 1 PART NO. A25001-nAB-03T1
TITLE 2.5mm pitch 180° WAFER-SMT TYPE					