

REV.	DESCRIPTION	DATE
A/0	初版发行	2013.10.13
B/0	升 B 版	2024.8.21






技术参数:

- 1、所有材料符合ROHS2.0/REACH要求。
- 2、额定电流: 3A, AC, DC;
- 3、额定电压: 250V, AC, DC;
- 4、温度范围: $-25^{\circ}\text{C}\sim+85^{\circ}\text{C}$;
- 5、接触电阻: $\leq 0.02\Omega$;
- 6、绝缘电阻: $\geq 1000\text{M}\Omega$;
- 7、耐压: 1000V, AC/minute.
- 8、产品料号:


A25002 - n AW - 02 T1

孔位
产品类型
AW: 弯插针座
电镀
T1: 镀亮锡
胶芯材质
02: PA66 米色

Circuits	Dimensions (mm)			
	A	B	C	D
02	2.50	6.10	7.50	3.10
03	5.00	8.60	10.00	3.10
04	7.50	11.10	12.50	3.60
05	10.00	13.60	15.00	6.10
06	12.50	16.10	17.50	8.60
07	15.00	18.60	20.00	11.10
08	17.50	21.10	22.50	13.60
09	20.00	23.60	25.00	16.10
10	22.50	26.10	27.50	18.60
11	25.00	28.60	30.00	21.10
12	27.50	31.10	32.50	23.60
13	30.00	33.60	35.00	26.10
14	32.50	36.10	37.50	28.60
15	35.00	38.60	40.00	31.10
16	37.50	41.10	42.50	33.60



SUGGESTED PCB LAYOUT
(COMPONENT SIDE)



2PIN外观

2	端子 Contact	黄铜	n×1	电镀层: 整体镀层厚度 30u"MIN, 局部镀 80u"MIN.
1	载 Wafer	PA66 (UL94V-0)	1	枪
序号	名称	材料	数量	附注

GENERAL TOLERANCES				DRAWN BY 罗荣程/2024.8.21		浙江深海电子有限公司	
0.X	±0.25	X.°	±3°	CHK. BY	朱江浩/2024.8.21		
0.XX	±0.12			APRV. BY	姚 婷/2024.8.21	SHEET	PROD. NAME SH-XHB2.54-NPW-MS
0.XXX	±0.05	X.X°	±0.5°	DRAWING NO. H25018-00		1 OF 1	PART NO. A25002-nAW-02T1
UNIT	SIZE	SCALE		TITLE			
MM	A4	1:1		2.5mm pitch 90° WAFER-DIP TYPE			