




技术参数:

- 1、所有材料符合ROHS2.0/REACH要求。
- 2、额定电流: 7A, AC, DC;
- 3、额定电压: 250V, AC, DC;
- 4、温度范围: -25℃~+105℃;
- 5、接触电阻: $\leq 0.02\Omega$;
- 6、绝缘电阻: $\geq 1000M\Omega$;
- 7、耐压: 1500V, AC/minute.
- 8、产品料号:

Circuits	Dimensions (mm)	
	A	B
02	3.96	7.92
03	7.92	11.88
04	11.88	15.84
05	15.84	19.80
06	19.80	23.76
07	23.76	27.72
08	27.72	31.68
09	31.68	35.64
10	35.64	39.60
11	39.60	43.56
12	43.56	47.52
13	47.52	51.48
...	...	...
20	75.24	79.20

GENERAL TOLERANCES				DRAWN BY	罗荣程/2024.8.17		浙江深海电子有限公司			
0.X ±0.25 X° ±3°				CHK. BY	朱江浩/2024.8.17					
0.XX ±0.12										
0.XXX ±0.05 X.X° ±0.5°				APRV. BY	姚 婷/2024.8.17					
UNIT	SIZE	SCALE		DRAWING NO.	SHEET	PROD. NAME			SH-VH3.96-NP-MS	
MM	A4	1:1		H39604-00	1 OF 1	PART NO.	A39601-nA-02T1			
TITLE										
3.96mm pitch 180° WAFER-DIP TYPE										



SUGGESTED PCB LAYOUT
(COMPONENT SIDE)