




REV	ECN NO.	DESCRIPTION	DESIGN	APPROVAL	DATE
A1	NEW	新版发行			2025.11.20

SPECIFICATIONS

- Current rating: 1A AC, DC
- Temperature range: -40°C ~ +105°C
- Insulation resistance: 500MΩ Min.
- Withstanding voltage: 300V AC/ minute.
- Contact resistance: 20mΩ Max.

Material:

Insulator Material:PA9T (UL 94V-0)

Contact Material:Brass

Plating:Matte Tin or gold plated over Nickel

Mate with XFCN PM127 Double Row series

Ordering Code:

PZ127V-22-XX-A40-2030

1.序列号

2.Pin位数:2*02=04P

No. of Pin/Row	Dimension	
	A	B
2*02	1.27	2.54
2*03	2.54	3.81
2*04	3.81	5.08
2*05	5.08	6.35
2*06	6.35	7.62
2*07	7.62	8.89
2*08	8.89	10.16
2*09	10.16	11.43
2*10	11.43	12.70
2*11	12.70	13.97
2*12	13.97	15.24
2*13	15.24	16.51
2*14	16.51	17.78
2*15	17.78	19.05
2*16	19.05	20.32
2*17	20.32	21.59
2*18	21.59	22.86
2*19	22.86	24.13
2*20	24.13	25.40
2*21	25.40	26.67
2*22	26.67	27.94
2*23	27.94	29.21
2*24	29.21	30.48
2*25	30.48	31.75
2*26	31.75	33.02
2*27	33.02	34.29
2*28	34.29	35.56
2*29	35.56	36.83
2*30	36.83	38.10
2*31	38.10	39.37
2*32	39.37	40.64
2*33	40.64	41.91
2*34	41.91	43.18
2*35	43.18	44.45
2*36	44.45	45.72
2*37	45.72	46.99
2*38	46.99	48.26
2*39	48.26	49.53
2*40	49.53	50.80
2*41	50.80	52.07
2*42	52.07	53.34
2*43	53.34	54.61
2*44	54.61	55.88
2*45	55.88	57.15
2*46	57.15	58.42
2*47	58.42	59.69
2*48	59.69	60.96
2*49	60.96	62.23
2*50	62.23	63.50

X.±0.50	X.°±	PART NO: PZ127V-22-XX-A40-2030		XFCN 兴飞连接器				
.X±0.25	.X°±							
.XX±0.15	.XX°±	TITLE: 1.27mm Pin Header Connectors		0769-82001899				
.XXX±0.10	.XXX°±			www.xfconn.com				
UNITS:	mm	APPD Chen ZhiQiang		DWG NO: /				
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF XFCN AND SHALL NOT BE REPRODUCED, COPIED OR CUED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF XFCN				CHKD Liu Wei		VIEW		
				DRAW Chen HongJiang		SCALE	SHEET	REV
				DATE 2025.11.20		NONE	1/1	A1