

REV.	DESCRIPTION	DATE
A/0	新版发行	2023.05.08
B/0	升 B 版	2024.8.6

技术参数:







- 1、所有材料符合ROHS2.0/REACH要求。
- 2、额定电流: 3.0A, AC, DC;
- 3、额定电压: 250V, AC, DC;
- 4、温度范围: -25℃~+85℃;
- 5、接触电阻: $\leq 0.02\Omega$;
- 6、绝缘电阻: $\geq 1000M\Omega$;
- 7、耐压: 800V, AC/minute.
- 8、适用线规: AWG#28 to #22
- 9、产品料号:

A20004 - n A - 02 T1
孔位 ———— A — 02 T1
产品类型 ————
A: 直针针座
T1: 镀亮锡
胶芯材质
02: PA66 米色

Circuits	Dimensions (mm)		
	A	B	C
2*2	2.00	4.90	6.00
2*3	4.00	6.90	8.00
2*4	6.00	8.90	10.00
2*5	8.00	10.90	12.00
2*6	10.00	12.90	14.00
2*7	12.00	14.90	16.00
2*8	14.00	16.90	18.00
2*9	16.00	18.90	20.00
2*10	18.00	20.90	22.00
2*11	20.00	22.90	24.00
2*12	22.00	24.90	26.00
2*13	24.00	26.90	28.00
2*14	26.00	28.90	30.00
2*15	28.00	30.90	32.00
2*16	30.00	32.90	34.00

2	端子 Contact	黄铜	n*2	电镀(镀): 整个表面镀厚30u"MIN, 厚镀锡 80u"MIN.
1	基座 Wafer	PA66 (UL94V-0)	1	绝
序号	名 称	材 料	数 量	附 注

GENERAL TOLERANCES				DRAWN BY	罗荣程/2024.8.6		浙江深海电子有限公司		
0.X	±0.25	X.°	±3°	CHK. BY	朱江浩/2024.8.6				
0.XX	±0.12			APRV. BY	姚 涛/2024.8.6				
0.XXX ±0.05 X.X° ±0.5°					SHEET	PROD. NAME SH-PHD-2*N			
UNIT	SIZE	SCALE		DRAWING NO.	1 OF 1	PART NO. A20004-nA-02T1			
MM	A4	1:1		H20021-00	TITLE 2.0mm pitch 180° WAFER-DIP TYPE				



SUGGESTED PCB LAYOUT
(COMPONENT SIDE)