






REV.	DESCRIPTION	DATE
A/0	初版发行	
B/0	升B版	2024.7.12




技术参数:
1、所有材料符合ROHS2.0/REACH法规。
2、额定电流: 2A, AC, DC;
3、额定电压: 100V, AC, DC;
4、温度范围: -25℃~+85℃;
5、接触电阻: ≤0.02Ω;
6、绝缘电阻: ≥1000MΩ;
7、耐压: 500V, AC/minute.
8、适用线规: AWG#32 to #24
9、产品料号:

A20001 - n A - 02 T1
孔位 — n
产品类型 — A
A: 直插针座
T1: 镀亮锡
胶芯材质
02: PA66 米色

Circuits	Dimensions (mm)		
	A	B	C
02	2.00	6.00	1.00
03	4.00	8.00	2.00
04	6.00	10.00	4.00
05	8.00	12.00	6.00
06	10.00	14.00	8.00
07	12.00	16.00	10.00
08	14.00	18.00	12.00
09	16.00	20.00	14.00
10	18.00	22.00	16.00
11	20.00	24.00	18.00
12	22.00	26.00	20.00
13	24.00	28.00	22.00
14	26.00	30.00	24.00
15	28.00	32.00	26.00
16	30.00	34.00	28.00
17	32.00	36.00	30.00
18	34.00	38.00	32.00
19	36.00	40.00	34.00
20	38.00	42.00	36.00

2	端子 Contact	黄铜	n×1	电镀: 整个表面镀层30u"MIN, 再镀锡 80u"MIN.
1	基座 Wafer	PA66(UL94V-0)	1	米色
序号	名称	材料	数量	附注



SUGGESTED PCB LAYOUT
(COMPONENT SIDE)

GENERAL TOLERANCES			DRAWN BY	刘焕刚/2024.7.12	浙江深海电子有限公司		
0.X	±0.25	X° ±3°	CHK. BY	朱江浩/2024.7.12			
0.XX	±0.12		APRV. BY	姚 婷/2024.7.12			
0.XXX	±0.05	X.X° ±0.5°			SHEET	PROD. NAME	SH-PH2.0-NP-MS
UNIT	SIZE	SCALE	DRAWING NO.		1 OF 1	PART NO.	A20001-nA-02T1
MM	A4	1:1	H20003-00		TITLE 2.0mm pitch 180° WAFER-DIP TYPE		