

90种型号， 每种 25 颗， 一共2250颗， 清单如下：

序号	体积	容量	精度	电压
1	0603	0.5PF	±0.25PF	50V
2	0603	0.75PF	±0.25PF	50V
3	0603	1PF	±0.25PF	50V
4	0603	1.2PF	±0.25PF	50V
5	0603	1.5PF	±0.25PF	50V
6	0603	1.8PF	±0.25PF	50V
7	0603	2PF	±0.25PF	50V
8	0603	2.2PF	±0.25PF	50V
9	0603	2.4PF	±0.25PF	50V
10	0603	2.5PF	±0.25PF	50V
11	0603	2.7PF	±0.25PF	50V
12	0603	3PF	±0.25PF	50V
13	0603	3.3PF	±0.25PF	50V
14	0603	3.6PF	±0.25PF	50V
15	0603	3.9PF	±0.25PF	50V
16	0603	4PF	±0.25PF	50V
17	0603	4.3PF	±0.25PF	50V
18	0603	4.7PF	±0.25PF	50V
19	0603	5PF	±0.25PF	50V
20	0603	5.1PF	±0.5PF	50V
21	0603	5.6PF	±0.5PF	50V
22	0603	6PF	±0.5PF	50V
23	0603	6.2PF	±0.5PF	50V
24	0603	6.8PF	±0.5PF	50V
25	0603	7PF	±0.5PF	50V
26	0603	7.5PF	±0.5PF	50V
27	0603	8PF	±0.5PF	50V
28	0603	8.2PF	±0.5PF	50V
29	0603	9.1PF	±0.5PF	50V
30	0603	10PF	±5%	50V
31	0603	11PF	±5%	50V
32	0603	12PF	±5%	50V
33	0603	13PF	±5%	50V
34	0603	15PF	±5%	50V
35	0603	16PF	±5%	50V
36	0603	18PF	±5%	50V
37	0603	20PF	±5%	50V
38	0603	22PF	±5%	50V
39	0603	24PF	±5%	50V
40	0603	27PF	±5%	50V
41	0603	30PF	±5%	50V
42	0603	33PF	±5%	50V
43	0603	36PF	±5%	50V
44	0603	39PF	±5%	50V
45	0603	43PF	±5%	50V
46	0603	47PF	±5%	50V
47	0603	51PF	±5%	50V
48	0603	56PF	±5%	50V
49	0603	62PF	±5%	50V
50	0603	68PF	±5%	50V
51	0603	75PF	±5%	50V
52	0603	82PF	±5%	50V

53	0603	91PF	±5%	50V
54	0603	100PF	±5%	50V
55	0603	110PF	±5%	50V
56	0603	120PF	±5%	50V
57	0603	130PF	±5%	50V
58	0603	150PF	±5%	50V
59	0603	160PF	±5%	50V
60	0603	180PF	±5%	50V
61	0603	200PF	±5%	50V
62	0603	220PF	±10%	50V
63	0603	270PF	±10%	50V
64	0603	330PF	±10%	50V
65	0603	390PF	±10%	50V
66	0603	470PF	±10%	50V
67	0603	560PF	±10%	50V
68	0603	680PF	±10%	50V
69	0603	820PF	±10%	50V
70	0603	1NF	±10%	50V
71	0603	1.2NF	±10%	50V
72	0603	1.5NF	±10%	50V
73	0603	2.2NF	±10%	50V
74	0603	3.3NF	±10%	50V
75	0603	4.7NF	±10%	50V
76	0603	6.8NF	±10%	50V
77	0603	8.2NF	±10%	50V
78	0603	10NF	±10%	25V
79	0603	15NF	±10%	25V
80	0603	22NF	±10%	25V
81	0603	33NF	±10%	16V
82	0603	47NF	±10%	16V
83	0603	68NF	±10%	16V
84	0603	82NF	±10%	16V
85	0603	100NF	±10%	16V
86	0603	220NF	±10%	16V
87	0603	470NF	±10%	16V
88	0603	680NF	±10%	10V
89	0603	1UF	±10%	10V
90	0603	2.2UF	±10%	6.3V