





REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-25^{\circ}\text{C}\sim 85^{\circ}\text{C}$.
3. 额定电压: 125V AC/DC.
4. 额定电流: 2.0A AC
DC(AWG#24, 0.D1.4mm MAX)
5. 接触电阻: $\leq 40\text{m}\Omega$.
6. 绝缘电阻: $\geq 1000\text{M}\Omega$.
7. 耐压: 500V AC/Minute



适用线路板(PCB LAYOUT)




P/N	PIN	DIM A	DIM B	DIM C
JXT-MX2.0-2PWT	2	10.90	4.80	2.00
JXT-MX2.0-3PWT	3	12.60	6.80	4.00
JXT-MX2.0-4PWT	4	14.60	8.80	6.00
JXT-MX2.0-5PWT	5	16.60	10.80	8.00
JXT-MX2.0-6PWT	6	18.60	12.80	10.00
JXT-MX2.0-7PWT	7	20.60	14.80	12.00
JXT-MX2.0-8PWT	8	22.60	16.80	14.00
JXT-MX2.0-9PWT	9	24.60	18.80	16.00
JXT-MX2.0-10PWT	10	26.60	20.80	18.00
JXT-MX2.0-11PWT	11	28.60	22.80	20.00
JXT-MX2.0-12PWT	12	30.60	24.80	22.00
JXT-MX2.0-13PWT	13	32.60	26.80	24.00
JXT-MX2.0-14PWT	14	34.60	28.80	26.00
JXT-MX2.0-15PWT	15	36.60	30.80	28.00

序号 (NO.)	品名 (Name)	材质 (Material)
1	MX2.0 Pitch B型 卧式WTB胶芯	PA9T UL94 V-0, 颜色:本色
2	MX2.0 Pitch B型 卧式WTB端子	铜合金/表面镀锡
3	MX2.0 Pitch B型 卧式WTB焊片	铜合金/表面镀锡

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.X:±0.35	X.X':±3"	PART NO. JXT-MX2.0-NPWT	TITLE: MX2.0 Pitch B型 卧式 WTB		
X.XX:±0.25	X.XX':±2"				
X.XXX:±0.15					
UNITS	mm	DESIGN:	Ethan	MANUFACTURE DWG	
MATERILA	— — —	CHED:	Olvia		SCALE
FINISH	— — —	APPD:	Ava		SHEET
				N:A	1/2

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN



TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.X:±0.35	X.X':±3°	PART NO. JXT-MX2.0-NPWT	TITLE: MX2.0 Pitch B型 卧式 WTB		
X.XX:±0.25	X.XX':±2°				
X.XXX:±0.15					
UNITS	mm	DESIGN:	Ethan	MANUFACTURE DWG	
MATERILA	— — —	CHED:	Olvia		
FINISH	— — —	APPD:	Ava		SCALE N:A SHEET 1/2