



部件材质工艺说明:

序号	物料名称	产品描述	数量
①	Antenna element	25*25*4 Ceramics	1
②	Installation method	Magnet+3M胶	1
③	COVER	43.5*39.5*15mm ABS+PC BLACK	1
④	CABLE	RG174 Copper COAXIAL CABLE 50ohm BLACK	1
⑤	CONNECTOR	FAKRA-C	1



MAIN TECHNICAL SPECIFICATIONS	
Frequency Range	1561±15.75MHz
Band Width	>5MHz
Axial ratio	≤4 DB
Vswr	≤2.0
Gain	LAN 28±2DBI
Impedance	50 OHM
Polarization	RHCP
Noise Figure	≤1.8 DB
DC Voltage	3.3-5V
DC Current	≤24mA
Connector	FAKRA-C
CABLE	RG174=1000mm
Dielectric Size	43.5*3*18
Working Temp	-40° -- 85°
Way To Install	Magnet+3M胶

1000±20mm

④

RG174全铜线

⑤



FAKRA-C型蓝色母头母针
(灰色色卡子)

备注:

- 1: 图中所标注尺寸为 I Q C 必测尺寸.
- 2: 各零部件组装要牢固可靠.
- 3: 成品信号参数要达到指定数值.
- 4: 产品需定数按要求包装好, 运输过程中不能有明显挤压变形等现象.
- 5: 未经我司确认, 材质及工艺要求等不能随意更改.

ZKT®

深圳市中科无线技术有限公司

公 差	x.	±0.30				代 码		料 号	
	x.x	±0.20				品 名	GNSS有源外置天线		
	x.xx	±0.10							
	ANGULAR® 5~	变 更 记 录		日 期	变更者	型 号	ZKA101342		
图 法		比 例		纸 张	A4	绘 图	ZHANG	日 期	2025. 12. 30
		单 位	MM	版 本	A	审 核		确 认	