







技术指标(Technical Index):



1. 温度范围(Temperature range): $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$.
2. 额定电压(Rated voltage): 100V, AC.
3. 额定电流(Rated current): 1.0A AC, DC.
4. 接触电阻(Contact resistance): $\leq 20\text{m}\Omega$.
5. 绝缘电阻(Insulation resistance): $\geq 500\text{M}\Omega$.
6. 耐压值(Withstanding voltage): 500V AC/minute.



REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

Part No	CKT	A	B
AZH1.5-2A-12	2	1.5	4.5
AZH1.5-3A-12	3	3.0	6.0
AZH1.5-4A-12	4	4.5	7.5
AZH1.5-5A-12	5	6.0	9.0
AZH1.5-6A-12	6	7.5	10.5
AZH1.5-7A-12	7	9.0	12.0
AZH1.5-8A-12	8	10.5	13.5
AZH1.5-9A-12	9	12.0	15.0
AZH1.5-10A-12	10	13.5	16.5
AZH1.5-11A-12	11	15.0	18.0
AZH1.5-12A-12	12	16.5	19.5
AZH1.5-13A-12	13	18.0	21.0
AZH1.5-14A-12	14	19.5	22.5
AZH1.5-15A-12	15	21.0	24.0
AZH1.5-16A-12	16	22.5	25.5
AZH1.5-17A-12	17	24.0	27.0
AZH1.5-18A-12	18	25.5	28.5
AZH1.5-19A-12	19	27.0	30.0
AZH1.5-20A-12	20	28.5	31.5

序号	品名	材质			
①	ZH1.5直针WTB胶芯	LCP UL94V-0 本色			
②	ZH1.5直针WTB端子	铜合金／表面镀锡			
TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.±0.50	±1°	PART NO. AZH1.5-NA-12	TITLE: ZH1.5直针WTB		
X.X±0.20					
X.XX±0.10					
UNITS	mm	DESIGN: Ethan	MANUFACTURE DWG		
MATERILA	— — —	CHED: Olivia			
FINISH	— — —	APPD: Ava			
			SCALE N:A	SHEET 1/2	



TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd				
X.±0.50	±2*	PART NO.		TITLE:		
X.X±0.25		AZH1.5-NA-12		ZH1.5直针WTB载带包装		
X.XX±0.15		DESIGN: Ethan		MANUFACTURE DWG		
UNITS	mm	CHED: Olivia				
MATERILA	— — —	APPD: Ava			SCALE	SHEET
FINISH	— — —				N:A	2/2