





#### 技术指标(Technical Index):






- 1.温度范围(Temperature range): $-25^{\circ}\text{C}\sim+85^{\circ}\text{C}$ .
- 2.额定电压(Rated voltage):250V,AC.
- 3.额定电流(Rated current):3.0A AC,DC.
- 4.接触电阻(Contact resistance): $\leq 20\text{m}\Omega$ .
- 5.耐压值(Withstanding voltage):1000V AC/minute.
- 6.绝缘电阻(Insulation resistance): $\geq 1000\text{M}\Omega$ .




| REV. | ECN NO. | DESCRIPTION | DATE | DESIGN |
|------|---------|-------------|------|--------|
|      |         |             |      |        |

| Part No        | CKT | A    | B    |
|----------------|-----|------|------|
| AXH2.54-2A-22  | 2   | 2.5  | 7.5  |
| AXH2.54-3A-22  | 3   | 5.0  | 10.0 |
| AXH2.54-4A-22  | 4   | 7.5  | 12.5 |
| AXH2.54-5A-22  | 5   | 10.0 | 15.0 |
| AXH2.54-6A-22  | 6   | 12.5 | 17.5 |
| AXH2.54-7A-22  | 7   | 15.0 | 20.0 |
| AXH2.54-8A-22  | 8   | 17.5 | 22.5 |
| AXH2.54-9A-22  | 9   | 20.0 | 25.0 |
| AXH2.54-10A-22 | 10  | 22.5 | 27.5 |
| AXH2.54-11A-22 | 11  | 25.0 | 30.0 |
| AXH2.54-12A-22 | 12  | 27.5 | 32.5 |
| AXH2.54-13A-22 | 13  | 30.0 | 35.0 |
| AXH2.54-14A-22 | 14  | 32.5 | 37.5 |
| AXH2.54-15A-22 | 15  | 35.0 | 40.0 |
| AXH2.54-16A-22 | 16  | 37.5 | 42.5 |

| 序号        | 品名           | 材质                                                                 |                      |              |              |
|-----------|--------------|--------------------------------------------------------------------|----------------------|--------------|--------------|
| ①         | XH2.5直针WTB胶芯 | LCP UL94V-0<br>米色 白色                                               |                      |              |              |
| ②         | XH2.5弯针WTB端子 | 铜合金/表面镀锡                                                           |                      |              |              |
| TOLERANCE |              | 深圳聚兴泰电子科技有限公司<br>Shenzhen Juxingtai Electronic Technology Co., Ltd |                      |              |              |
| X.±0.50   | ±1°          | PART NO.<br>AXH2.54-NA-22                                          | TITLE:<br>XH2.5弯针WTB |              |              |
| .X±0.20   |              |                                                                    |                      |              |              |
| .XX±0.10  |              |                                                                    |                      |              |              |
| UNITS     | mm           | DESIGN: Ethan                                                      | MANUFACTURE DWG      |              |              |
| MATERILA  | — — —        | CHED: Olvia                                                        |                      |              |              |
| FINISH    | — — —        | APPD: Ava                                                          |                      | SCALE<br>N:A | SHEET<br>1/2 |



| 纸箱型号<br>Carton Type | 小型<br>Small Size | 中型<br>Medium | 标准型<br>Standard |
|---------------------|------------------|--------------|-----------------|
| 高度<br>Hight (CM)    | 7.5              | 15           | 32              |



| CKT<br>(2.5mm pitch) | B0    | W  | F     |
|----------------------|-------|----|-------|
| 2                    | 7.80  | 24 | 11.50 |
| 3                    | 10.30 |    |       |
| 4                    | 12.80 |    |       |

| CKT<br>(2.5mm pitch) | W  | PCS/RELL | RELL/CARTON | SUM(PCS) |
|----------------------|----|----------|-------------|----------|
| 2                    | 24 | 400      | 10          | 4000     |
| 3                    |    |          |             |          |
| 4                    |    |          |             |          |

NOTE(注):

- 1.10 SPROCKET HOLE PITCH CUMULATIVE TOLERANCE  $\pm 0.2\text{mm}$ .  
(10片孔距累积公差 $\pm 0.2\text{mm}$ .)
- 2.CARRIER CAMBER NOT TO EXCEED 1mm IN 100mm.  
(载带拱/弧形MAX:1/100mm.)
- 3.ALL DIMENSIONS MEET EIA-481 REQUIREMENTS.  
(所有的尺寸要满足协会EIA-481规范.)
- 4.MATERIAL: CLEAR ANTISTATIC PS, COLD SEALING.  
(载带材料: 透明防静电 PS, 冷封.)
- 5.THICKNESS:  $0.50 \pm 0.05\text{mm}$ . (载带厚度:  $0.50 \pm 0.05\text{mm}$ .)
- 6.PACKING LENGTH PER REEL: 6.72 METERS. (每卷包装长度: 6.72米.)
- 7.COMPONENT LOAD PER REEL: 400 PCS. (每卷包装数量: 400只, 前后各空10只.)
- 8.纸箱装箱以不超过装箱线为准, 空余位置用塑料泡沫及保尼龙填充.
- 9.纸箱分小、中、标准型3种规格型号: 装箱为整箱(左下包装量)采用标准型纸箱包装, 未达到整箱数量以产品量适当采用小型或中型纸箱包装.

| TOLERANCE      |               | 深圳聚兴泰电子科技有限公司<br>Shenzhen Juxingtai Electronic Technology Co., Ltd |                     |       |       |
|----------------|---------------|--------------------------------------------------------------------|---------------------|-------|-------|
| X. $\pm 0.50$  | $\pm 1^\circ$ | PART NO.<br>AXH2.54-NA-22                                          | TITLE:<br>XH2.5#WTB |       |       |
| .X $\pm 0.20$  |               |                                                                    |                     |       |       |
| .XX $\pm 0.10$ |               |                                                                    |                     |       |       |
| UNITS          | mm            | DESIGN: Ethan                                                      | MANUFACTURE DWG     |       |       |
| MATERIAL       | ---           | CHED: Olivia                                                       |                     | SCALE | SHEET |
| FINISH         | ---           | APPD: Ava                                                          |                     | N:A   | 2/2   |