









Part No	Pin	A	B	C
XY-FPC-1.0-CT-4P	4	3.00	5.03	11.10
XY-FPC-1.0-CT-5P	5	4.00	6.03	12.10
XY-FPC-1.0-CT-6P	6	5.00	7.03	13.10
XY-FPC-1.0-CT-7P	7	6.00	8.03	14.10
XY-FPC-1.0-CT-8P	8	7.00	9.03	15.10
XY-FPC-1.0-CT-9P	9	8.00	10.03	16.10
XY-FPC-1.0-CT-10P	10	9.00	11.03	17.10
XY-FPC-1.0-CT-11P	11	10.00	12.03	18.10
XY-FPC-1.0-CT-12P	12	11.00	13.03	19.10
.....		...		
XY-FPC-1.0-CT-40P	40	(40-1)*1.0	(40+1)*1.0+0.03	(40+1)*1.0+0.10



SECTION A-A



适用扁平线(Applicable Flat Cable)



适用线路板(PCB LAYOUT)

序号	品名	材质
1	1.0胶壳(H2.5)	LCP UL94V-0 本色
2	1.0上接端子(H2.5)	铜合金/表面镀锡
3	1.0降式后盖(H2.5)	LCP UL94V-0 黑色
4	1.0降式焊片(H2.5)	铜合金/表面镀锡

技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$ 。
3. 额定电压: 50V, AC/DC。
4. 接触电阻: $\leq 0.03\Omega$ 。
5. 绝缘电阻: $\geq 500\text{M}\Omega$ 。

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd				
TOLERANCE UNLESS OTHERWISE SPECIFIED						
.X±0.3	X.*±5°	APR.	Alex	TITLE: 1.0 Pitch H2.5 ZIF R/A Type Top CONN.		
.XX±0.2	.X*±2	CHK.	Jack	DWG NO. XY-FPC-1.0-CT-NP		
.XXX±0.05	.XX*±1°	DRA.	Can	PROJ. 		CUSTOMER DRAWING
				SIZE A4	SCALE 1:1	SHEET 1/1