










适用扁平线(Applicable Flat Cable)

Part No	Pin	A	B	C	D
XY-FPC-0.5-CTD-4P	4	1.50	2.56	7.60	5.20
XY-FPC-0.5-CTD-5P	5	2.00	3.06	8.10	
XY-FPC-0.5-CTD-6P	6	2.50	3.56	8.60	
XY-FPC-0.5-CTD-7P	7	3.00	4.06	9.10	
XY-FPC-0.5-CTD-8P	8	3.50	4.56	9.60	
XY-FPC-0.5-CTD-9P	9	4.00	5.06	10.10	
XY-FPC-0.5-CTD-10P	10	4.50	5.56	10.60	
XY-FPC-0.5-CTD-11P	11	5.00	6.06	11.10	
XY-FPC-0.5-CTD-12P	12	5.50	6.56	11.60	5.75
.....					
XY-FPC-0.5-CTD-34P	34	16.50	17.56	22.60	
XY-FPC-0.5-CTD-35P	35	17.00	18.06	23.10	
XY-FPC-0.5-CTD-36P	36	17.50	18.56	23.60	
.....		...			
XY-FPC-0.5-CTD-60P	60	(60-1)*0.5	(60+1)*0.5+0.06	(60+1)*0.5+0.1	



适用线路板(PCB LAYOUT)

序号	品名	材质
1	0.5拉拔端子(H2.0)	LCP UL94V-0 本色
2	0.5拉拔下接触子(H2.0)	铜合金/表面镀锡
3	0.5拉拔跨式后盖(H2.0)	LCP UL94V-0 黑色
4	0.5拉拔垫片(H2.0)	铜合金/表面镀锡

技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$ 。
3. 额定电压: 50V, AC/DC。
4. 接触电阻: $\leq 0.03\Omega$ 。
5. 绝缘电阻: $\geq 500M\Omega$ 。

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd				
TOLERANCE UNLESS OTHERWISE SPECIFIED						
.X±0.3	X.*± 5°	APR.	Alex	TITLE: 0.5 Pitch H2.0 ZIF R/A Type 3 Unper CONN.		
.XX±0.2	.X*± 2	CHK.	Jack	DWG NO. XY-FPC-0.5-CTD-NP		
.XXX±0.05	.XX*± 1°	DRA.	Can	PROJ.	CUSTOMER DRAWING	
				SIZE A4	SCALE 1:1	SHEET 1/1