


Technical Data
Material:
Contact material:Brass
Plating:Gold Flash
Insulator material:Black polyester UL94V-0
Standard:PA6T+30%G.F

Electrical:
Current rating:1.5Amps/contact max.
Contact resistance:≤20mΩ/contact
Insulation resistance:≥1000MΩ at V=100V
Withstanding Voltage:450V AC/minute

PCB Layout

Mechanical:
Soldering temperature:+260℃, 4s max

UNSPECIFIED TOLERANCE: ±0.20



A=2.0* η P+0.50±0.50
B=2.0* η P-2.0±0.20
Pin Number=1~40

APPROVALS				DATE			
DRAWN				G.M.Chen			
CHECKED				2015/5/22			
APPROVALS				TITLE: 2.00mm Female Header Connectors			
TOLERANCES ARE				PART NO. DW200R-11-XX-63			
30 $\pm$ 0.15				ANGLE			
10 $\pm$ 0.30				UNIT: mm			
5 $\pm$ 0.10				SCALE: 1:1			
~5				DRAWING NO.			
±2'				SHEET 1 OF 1			
PROJ. 1				PROJ. 1			

DEALON 德之隆®
ELECTRONICS CO.,LTD