


序号	品名	材质
1	0.5mm厚板(H2.0)	LCP UL94V-0 本色
2	0.5mm厚板(H2.0)	铜合金/表面镀金
3	0.5mm厚板(H2.0)	LCP UL94V-0 黑色
4	0.5mm厚板(H2.0)	铜合金/表面镀金


技术指标:

1. 零件表面应光滑、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-25^{\circ}\text{C}\sim 85^{\circ}\text{C}$ 。
3. 额定电压: 50V, AC/DC(等效)。
4. 接触电阻: $\leq 0.03\Omega$ 。
5. 绝缘电阻: $>500\text{M}\Omega$ 。


Part No	Pin	A	B	C
XY-FPC-1.0-10-2P	2	1.00	3.10	6.90
XY-FPC-1.0-10-3P	3	2.00	4.10	7.90
XY-FPC-1.0-10-4P	4	3.00	5.10	8.90
XY-FPC-1.0-10-5P	5	4.00	6.10	9.90
XY-FPC-1.0-10-6P	6	5.00	7.10	10.90
XY-FPC-1.0-10-7P	7	6.00	8.10	11.90
XY-FPC-1.0-10-8P	8	7.00	9.10	12.90
XY-FPC-1.0-10-9P	9	8.00	10.10	13.90
XY-FPC-1.0-10-10P	10	9.00	11.10	14.90
*****	****	***	*****	*****
XY-FPC-1.0-10-32P	32	(32-1)*1.0	(32+1)*1.0+0.10	(32+6)*1.0-0.10



4~9 PIN 插针样式



适用线路板(PCB LAYOUT)



Applicable Flat Cable

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED		APR.	Alex	TITLE: 1.0 Pitch 插针式下接 (H=2.0)	
.X $\pm$ 0.3	X.* $\pm$ 5°	CHK.	Jack	DWG NO. XY-FPC-1.0-10-NP	
.XX $\pm$ 0.2	.X* $\pm$ 2	PROJ.	Can	CUSTOMER DRAWING	
.XXX $\pm$ 0.05	.XX* $\pm$ 1°	SIZE	A4	SCALE	1:1
		SHEET	1/1	REV.	A