






- Note:
- Material:
 - Housing: thermoplastic high temp.UL94V-0; Color: natural.
 - Latch: thermoplastic high temp.UL94V-0; Color: black.
 - Terminal: copper alloy.
 - Fitting Nail: copper alloy.
 - Finish:
 - Terminal:
 - Underplating: Au/matt Tin overall.
 - Fitting Nail:
 - Underplating: matt Tin overall.
 - Product must comply HF RoHS specification.



CKTS	DIM A	DIM B	DIM C	DIM D
4	3.00	5.10	9.05	11.00
5	4.00	6.10	10.05	12.00
6	5.00	7.10	11.05	13.00
7	6.00	8.10	12.05	14.00
8	7.00	9.10	13.05	15.00
9	8.00	10.10	14.05	16.00
10	9.00	11.10	15.05	17.00
11	10.00	12.10	16.05	18.00
12	11.00	13.10	17.05	19.00
13	12.00	14.10	18.05	20.00
14	13.00	15.10	19.05	21.00
15	14.00	16.10	20.05	22.00
16	15.00	17.10	21.05	23.00
17	16.00	18.10	22.05	24.00
18	17.00	19.10	23.05	25.00
19	18.00	20.10	24.05	26.00
20	19.00	21.10	25.05	27.00
21	20.00	22.10	26.05	28.00
22	21.00	23.10	27.05	29.00
23	22.00	24.10	28.05	30.00
24	23.00	25.10	29.05	31.00
25	24.00	26.10	30.05	32.00
26	25.00	27.10	31.05	33.00
27	26.00	28.10	32.05	34.00
28	27.00	29.10	33.05	35.00
29	28.00	30.10	34.05	36.00
30	29.00	31.10	35.05	37.00







CUSTOMER DRAWING


LXW 连兴旺电子(深圳)有限公司
connectivity LXWCONN ELECTRONICS (SHENZHEN) CO., LTD

Tolerance Unspecified (未注公差): 0.0 ±0.15 0° ±5° 0.00 ±0.10 0° ±3° 0.000 ±0.05 0° ±1°	Size (图幅): A4 Unit (单位): MM Scale (比例): 1:1	Product Name (产品名称): 1.0Pitch H=2.5 FPC ZIF R/A Lower TypeK1 SMT CONN Product No (产品料号): LF2125-XXXS-WOR
Project View (投影视角): 1 OF 1	Page (页数): 1 OF 1	Designer (设计): Allan 03/23/11 Checked (审核): Approved (核准):

Rev 版本	Change Description 变更内容	Date 日期	Revisior 制/修订人
A	初版发行	2011/03/23	Allan






SECTION A-A
SCALE 1:1



DETAIL B
SCALE 5:1

NOTES:

1. 10 SPROCKET HOLE PITCH CUMULATIVE TOLERANCE.±0.20mm
2. CARRIER CAMBER NOT TO EXCEED 1mm IN 250mm.
3. ALL DIMENSIONS MEET EIA-481-C REQUIREMENTS.
4. MATERIAL: BLACK ANTI-STATIC POLYSTYRENE.
5. THICKNESS: 0.35 ± 0.05 mm.
6. PACKING LENGTH PER 13" REEL : 18.60METERS.
7. COMPONENT LOAD PER 13" REEL : 1500PCS
8. PEELING OFF FORCE OF TOP TAPE 0.1N~0.7N(10.2gf~100gf).



CKTS	30±0.10	W	WI	F	S0±0.10
4	11.30				
5	12.30				
6	13.30	24±0.3/-0	24.4	11.5±0.10	单边孔
7	14.30				
8	15.30				
9	16.30				
10	17.30				
11	18.30	32±0.30	32.4	14.2±0.10	28.4
12	19.30				
13	20.30				
14	21.30				
15	22.30				
16	23.30				
17	24.30				
18	25.30				
19	26.30				
20	27.30				
21	28.30	44±0.30	44.4	20.2±0.15	40.4
22	29.30				
23	30.30				
24	31.30				
25	32.30				
26	33.30				
27	34.30				
28	35.30				
29	36.30	56±0.30	56.4	26.2±0.15	52.4
30	37.30				

CLASSIFICATION DIMENSION (尺寸类别):
 FAI (首次检验): ⊕ To ⊕
 ■ MARK IS MAJOR DIM (重点尺寸标示)
 * ⊗ MARK IS CRITICAL DIM (Cp&Cp 标示)

Tolerance Unspecified (未注公差)
 0.0 ±0.10 0° ±3°
 0.00 ±0.05 0° 0 ±2°
 0.000 ±0.02 0° 00 ±1°

Size (图框): A4
 Unit (单位): MM
 Scale (比例): 1:1

Project View (投影规则): 10 OF 10
 Rev (版本): 1.0

LXW 连兴旺电子(深圳)有限公司
 connectivity LXWCONN ELECTRONICS (SHENZHEN) CO., LTD

Product Name (产品名称): 1.0Pitch H=2.5 FPC ZIF R/A Lower TypeK1 SMT CONN

Product No (产品料号): LF2125-XXXX-WOR

Drawing No (图面编号): DNE00015-1
 Date (日期): 2011/04/09

Designer (设计): Allan 04/09'11
 Checked (审核):
 Approved (核准):

Rev	Date	Revisor
1.0	2011/04/09	Allan
初版发行		
变更内容		

