









Applicable FPC

Note:

1.Material

- 1.1: Housing: LCP UL94-V0 Color:Natural.
- 1.2: Actuator: High Temperature UL94-V0 Color:Black
- 1.3: Contact: Phosphor Bronze.
- 1.4: LEG: Phosphor Bronze.

2.Plating

- 2.1: Contact: See Part Number.
- 2.2: LEG: Matte Tin Plating Over Nickel.


3.Rating:

- 3.1: Operating Voltage: 30V AC/DC.
- 3.2: Current Rating: 0.2A AC/DC.
- 3.3: Operating Temperature:-55°C~+85°C.



DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd				
TOLERANCE UNLESS OTHERWISE SPECIFIED						
.X±0.3	X.*±5°	APR.	Alex	TITLE: FPC 0.3Pitch 1.0H ZIF R/A Connector		
.XX±0.2	.X.*±2	CHK.	Jack	DWG NO. XY-FPC-0.3-10-NP		
.XXX±0.05	.XX.*±1°	DRA.	Can	PROJ. 		CUSTOMER DRAWING
				SIZE A4	SCALE 1:1	SHEET 1/1

EMBOSSED TAPE PACKING


0.3mm Pitch FPC Connector, ZIF R/A SMT Type



SCALE 1:4



PIN NO.	W	A	B	C	PCS /REEL	REEL/CARTON	SUM(PCS)
13PIN~25PIN	20.5	16	7.50	—	5000	13	65000
27PIN~49PIN	28.5	24	11.5	—	5000	10	50000
51PIN~61PIN	36.5	32	14.2	28.4	5000	8	40000
67~73PIN	48.5	44	20.2	40.4	5000	6	30000



DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED		TITLE: FPC 0.3Pitch 1.0H ZIF R/A Connector			
.X±0.3	X.*± 5°	APR.	Alex	DWG NO. XY-FPC-0.3-10-NP	
.XX±0.2	.X.*± 2	CHK.	Jack	PROJ.  CUSTOMER DRAWING	
.XXX±0.05	.XX.*± 1°	DRA	Can	SIZE A4	SCALE 1:1
		SHEET 1/1		REV.	A