

Part No	Pin	A	B	C	D	E
XY-FPC-0.3-09-9P	9	4.90	1.80	2.40	3.03	4.37
XY-FPC-0.3-09-11P	11	5.50	2.40	3.00	3.63	4.97
XY-FPC-0.3-09-13P	13	6.10	3.00	3.60	4.23	5.57
XY-FPC-0.3-09-15P	15	6.70	3.60	4.20	4.83	6.17
XY-FPC-0.3-09-21P	21	8.50	5.40	6.00	6.63	7.97
XY-FPC-0.3-09-23P	23	9.10	6.00	6.60	7.23	8.57
XY-FPC-0.3-09-25P	25	9.70	6.60	7.20	7.83	9.17
XY-FPC-0.3-09-31P	31	11.50	8.40	9.00	9.63	10.97
XY-FPC-0.3-09-33P	33	12.10	9.00	9.60	10.23	11.57
XY-FPC-0.3-09-35P	35	12.70	9.60	10.20	10.83	12.17
XY-FPC-0.3-09-39P	39	13.90	10.80	11.40	12.03	13.37
XY-FPC-0.3-09-41P	41	14.50	11.40	12.00	12.63	13.97
XY-FPC-0.3-09-45P	45	15.70	12.60	13.20	13.83	15.17
XY-FPC-0.3-09-51P	51	17.50	14.40	15.00	15.63	16.97

Note:

1.Material

1.1: Housing: LCP UL94-V0 Color:Natural.

1.2: Actuator: High Temperature UL94-V0

Color:Black

1.3: Contact: Phosphor Bronze.

1.4: LEG: Phosphor Bronze.

2.Plating

2.1: Contact: See Part Number.


2.2: LEG: Matte Tin Plating Over Nickel.

3.Rating:

3.1: Operating Voltage: 30V AC/DC.

3.2: Current Rating: 0.2A AC/DC.


3.3: Operating Temperature:-55°C~+85°C.



DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED		APR.	TITLE: FPC 0.3Pitch 1.0H ZIF R/A Connector 插		
.X±0.3	X.*± 5°	Alex	DWG NO. XY-FPC-0.3-09-NP		
.XX±0.2	.X*± 2	Jack	PROJ. CUSTOMER DRAWING		
.XXX±0.05	.XX*± 1°	Can	SIZE A4	SCALE 1:1	SHEET 1/1 REV. A



EMBOSSSED TAPE PACKING

0.3mm Pitch FPC Connector, ZIF R/A SMT Type




SAFE TAPE ⑮
(安全帯L=1750mm Ref)

SCALE 1:4



PIN NO.	W	A	B	C	PCS /REEL	REEL/CARTON	SUM(PCS)
9PIN~25PIN	16	20.5	7.50	—	4000	15	30000
31PIN~45PIN	24	28.5	11.5	—	4000	10	40000
51PIN	32	36.5	14.2	28.4	4000	8	32000



DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd				
TOLERANCE UNLESS OTHERWISE SPECIFIED						
.X±0.3	X.*± 5°	APR. Alex	TITLE: 0.3Pitch 1.0H ZIF R/A Connector 插			
.XX±0.2	.X*± 2	CHK. Jack	DWG NO. XY-FPC-0.3-09-NP			
.XXX±0.05	.XX*± 1°	DRA. Can	PROJ. 		CUSTOMER DRAWING	
			SIZE A4	SCALE 1:1	SHEET 1/1	REV. A