







CKT	A	B
2*2	2.0	6.0
2*3	4.0	8.0
2*4	6.0	10.0
2*5	8.0	12.0
2*6	10.0	14.0
2*7	12.0	16.0
2*8	14.0	18.0
2*9	16.0	20.0
2*10	18.0	22.0
2*11	20.0	24.0
2*12	22.0	26.0
2*13	24.0	28.0
2*14	26.0	30.0
2*15	28.0	32.0
2*16	30.0	34.0
2*17	32.0	36.0
2*18	34.0	38.0
2*19	36.0	40.0
2*20	38.0	42.0



技术指标 (Technical Index):

1. 工作温度 (Temperature range): $-25^{\circ}\text{C}\sim+85^{\circ}\text{C}$.
2. 额定电压 (Rated voltage): 250V DC/AC(rms).
3. 额定电流 (Rated current): 3.0A AC, DC.
4. 接触电阻 (Contact resistance): $\leq 20\text{m}\Omega$.
5. 耐压值 (Dielectric withstanding voltage): 800V AC/minute.
6. 绝缘电阻 (Insulation resistance): $\geq 1000\text{M}\Omega$.



APPROVALS		DATE		DRAWN		CHECKED		APPROVALS		TOLERANCES ARE		PART NO.		SCALE: 1:1		SHEET 1 OF 1	
DRAWN		G.M.Chen		2015/7/17		CHECKED		APPROVALS		30~0.15 10~0.30 5~0.10 ~5		±0.30 ±0.20 ±0.15 ±0.10		ANGLE		UNIT: mm	
DATE		2015/7/17		TITLE:		2.00mm Crimp Style Connectors		X2005WV-XXA		±2°		DRAWING NO.		PROJ		SHEET 1 OF 1	
ECN NO.		REV.		DATE		DESCRIPTION		CHANGE		CHECK		APPRO		NEW		A	