



材质 Material:

绝缘体 Insulator: Glass filled PBT ,Black

接触件 Contacts: Brass

电镀层 Plating: All Nickel plating

电气性能 Electrical Characteristics:

接触电阻 Contact Resistance: 20mΩmax. at DC 100mA

绝缘电阻 Insulator Resistance: 1000MΩmin. at 500V DC

耐压 Withstanding Voltage: 1000V AC/rms 50Hz For 1 minute

工作电流 Current Rating: 3 AMP

使用温度范围 Operating Temperature: -55℃ ~ +105℃

电缆规格 Cable: 1.27mm (0.050") pitch flat cable

Dimension

Position	A	B	C
2*3	12.22	5.08	6.35
2*4	14.76	7.62	8.89
2*5	17.30	10.16	11.43
2*6	19.84	12.70	13.97
2*7	22.38	15.24	16.51
2*8	24.92	17.78	19.05
2*9	27.46	20.32	21.59
2*10	30.00	22.86	24.13
2*11	32.54	25.40	26.67
2*12	35.08	27.94	29.21
2*13	37.62	30.48	31.75
2*14	40.16	33.02	34.29
2*15	42.70	35.56	36.83
2*16	45.24	38.10	39.37
2*17	47.78	40.64	41.91
2*18	50.32	43.18	44.45
2*20	55.40	48.26	49.53
2*22	60.48	53.34	54.61
2*25	68.10	60.96	62.23
2*30	80.80	73.66	74.93
2*32	85.88	78.74	80.01

TITLE 简牛I.D.C SOCKET 2.54
mm 2.54FC扁平电缆连接器

RPAT NO: XDHF-0258-2* N P

GENERAL TOLERANCE

x. : ±0.3
x.x: ±0.2
x.xx: ±0.1

ANGLE TOLERANCE

x. : ±2°
x.x: ±1°
x.xx: ±0.5°

DRAWN BY DATE

CHECKED BY DATE

APPROVED BY DATE

深圳市连欣科技有限公司
ShenzhenCity Lianxin Technology Co., Ltd

DRAWING NO. SHEET 1 OF 1

SHEET SIZE A4 REV. A0

SCALE	DESCRIPTION	CHK	DATE
1	2	3	4