




Poles	Dimensions (mm)	
	A	B
1	2.50	7.50
2	5.00	10.00
3	10.00	12.50
4	10.00	15.00
5	12.50	17.50
6	15.00	20.00
7	17.50	22.50
8	20.00	25.00
9	22.50	27.50
10	25.00	30.00
11	27.50	32.50
12	30.00	35.00
13	32.50	37.50
14	35.00	40.00
15	37.50	42.50
16		



P.C.B LAYOUT

- 技术指标:
1. 塑体表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
 2. 温度范围: -25° C~85° C.
 3. 额定电压: 50V, AC, DC.
 4. 接触电阻: ≤0.02Ω.
 5. 绝缘电阻: ≥100MΩ

APPROVALS				DATE	
DRAWN	G.M.Chen	2015/7/17			
CHECKED					
APPROVALS					
TOLERANCES ARE		30~0.15 10~0.30 5~10	±0.30 ±0.20 ±0.15	ANGLE	±2°
PART NO.		XHB-W-XXA		UNIT: mm	SCALE: 1:1
DRAWING NO.				SHEET 1 OF 1	
DRAWING NO.				PROJ. 1	

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			