




REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

Part No	CKT	A	B	C	D
ANH1.0-2A-32	2	1.00	2.52	4.00	3.00
ANH1.0-3A-32	3	2.00	3.52	5.00	4.00
ANH1.0-4A-32	4	3.00	4.52	6.00	5.00
ANH1.0-5A-32	5	4.00	5.52	7.00	6.00
ANH1.0-6A-32	6	5.00	6.52	8.00	7.00
ANH1.0-7A-32	7	6.00	7.52	9.00	8.00
ANH1.0-8A-32	8	7.00	8.52	10.00	9.00
ANH1.0-9A-32	9	8.00	9.52	11.00	10.00
ANH1.0-10A-32	10	9.00	10.52	12.00	11.00
ANH1.0-11A-32	11	10.00	11.52	13.00	12.00
ANH1.0-12A-32	12	11.00	12.52	14.00	13.00
ANH1.0-13A-32	13	12.00	13.52	15.00	14.00
ANH1.0-14A-32	14	13.00	14.52	16.00	15.00
ANH1.0-15A-32	15	14.00	15.52	17.00	16.00
ANH1.0-16A-32	16	15.00	16.52	18.00	17.00



技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-25^{\circ}\text{C}\sim 85^{\circ}\text{C}$ 。
3. 额定电压: 50V, AC, DC
4. 接触电阻: $\leq 0.02\Omega$ 。
5. 绝缘电阻: $\geq 100M\Omega$



序号	品名	材质	TOLERANCE	深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
①	1.0-B型立式WTB胶芯	PA10T UL94V-0米白色	X.±0.50 ±1°	PART NO.	TITLE:		
②	1.0-B型立式WTB端子	铜合金/表面镀锡	X.X±0.20 X.XX±0.10	ANH1.0-NA-32	1.0 Pitch B型立式WTB		
③	1.0-B型立式WTB焊片	铜合金/表面镀锡	UNITS mm	DESIGN: Ethan	MANUFACTURE DWG		
④	1.0-B型立式WTB吸盖	LCP UL94V-0 本色	MATERILA — — — FINISH — — —	CHED: Olvia APPD: Ava	SCALE SHEET N:A 1/1		