



LED colour(LED颜色)	Part No. (料号)
Whiler(白色)	K6-6163D-01
Red(红色)	K6-6163D-02
Blue(蓝色)	K6-6163D-03
Green(普绿)	K6-6163D-04
Yellow(黄色)	K6-6163D-05
Orange(橙色)	K6-6163D-06
Jade green(翠绿色)	K6-6163D-07



PCB Layout (Top Side)



Circuit Diagram

Typical Specifications

- 1.Rating : DC 30V 30mA
- 2.Insulation Resistance : 100mΩ Min
- 3.Dielectric Strength : AC 250V for 1 minute
- 4.Operating Force : 260±50 gf
- 5.Contact Resistance : 50mΩ MAX
- 6.Life : 100,000 Cycles Min

④	Cap	—	1	ABS	Natural	_____
③	Contact	—	1	SUS	Ag Plating	_____
②	Terminal	—	6	Brass	Ag Plating	_____
①	Housing	—	1	PA66	Black	_____
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK
APPROVALS			DATE		DRAWN LIUCAN 2022.3.1	
CHECKED						
APPROVALS			TITLE: LED Tact Switch PART NO. K6-6163D		PROJ: 	
TOLERANCES ARE	30~以上 10~30 5~10 ~ 5	±0.30 ±0.20 ±0.15 ±0.10	ANGLE UNIT: mm SCALE: 1:1	DRAWING NO.		

—	A	—	NEW	—	—	—
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.