





linear dimension(Tolerances Standard GB/T 14486-2008)								—   		
variable range	to 6	over 6 to 10	over 10 to 30	over 30 to 60	over 60 to 100	over 100 to 160	over 160 to	to 10	over 10 to 100	over 100 to
tolerance	±0.20	±0.30	±0.50	±0.70	±1.00	±1.30	±1.60	0.10	0.30	0.60



PCB LAYOUT




REVISION RECORD				
REV.	DESCRIPTION	ECN No.	APPROVED	DATE
A	新发行		CLF	23.03.15

UL/CUL 技术 参数					
UL/CUL Technical Data					
等 级	Use Group	B	C	D	
额定电压	Rated Voltage	[V]	300	-	300
额定电流	Rated Current	[A]	10	-	10
接线范围	Wire Range	-			
单/多芯线	Solid/Stranded				[AWG]
耐电压	Withstanding Voltage	AC1600V/1Min			
IEC 技术参数					
IEC Technical Data					
过电压类别	Overvoltage Category	III	III	II	
污染等级	Contamination Class	3	2	2	
额定电压	Rated Voltage	[V]	-	320	630
额定电流	Rated Current	[A]	-	15	15
额定冲击电压	Impulse withstand voltagea	[KV]	-	4.0	4.0
导线截面积	Conductor cross section	-			
硬质/柔性导线	Solid/ flexible				[mm²]
材 料 Material					
绝缘材料	Insulation Material	PA66			
阻燃等级	Imflamability	UL94V-0			
导体材料	Contactur Material	铜合金 Copper alloy			
导体表面镀层	Contactive Coating	镀锡 Tin Plated			
一般参数 Other Data					
间距	Pitch	[mm]	5.0		
极数	Poles	[P]	2-24		
剥线长度	Stripping Length	[mm]	-		
螺丝	Screw/ 扭矩 Torque(Max)	[N.m]	-		
工作温度	Operating temperatur	[°C]	-40~+105		
引针尺寸	Pin Dimensions	[mm]	3.7		
PCB板孔径	PCB Hole Diameter	[mm]	1.6		

DES.	LQQ	DATE	23.03.15
CHK.	BY	DATE	23.03.15
APP.	CLF	DATE	23.03.15

单位 / UNITS	mm	尺寸 / SIZE	A4	比例 / SCALE	1:1
慈溪市科发电子有限公司 CIXI KEFA ELECTRONIC CO., LTD					

第三视角 / THIRD ANGLE PROJECTION		版本 / REV	A
		名称 / TITLE	KF2EDGV-5.0