



RoHS

MAPX

MODIFICATION

DRW

DATE



备注:

1.1 材质:

1.2 胶芯: LCP+30%G.F

1.3 端子: C2680-H, T=0.15mm; 镍底, 镀金1U"

1.4 外壳: SUS201-1/2H, T=0.30mm; 整体镀镍

1.5 中夹片: SUS301-1/2H, T=0.15mm

2. 主要特性:

2.1 额定电流: 3A

2.2 接触阻抗: 40mΩ MAX

2.3 绝缘阻抗: 100MΩ MIN 250V DC

2.4 耐压测试: 100V AC






2.5 沾锡性: 温度250±5℃, 时间5±0.5s

2.6 整体插入力: 2.0kgf MAX

耐久前整体拔出力: 0.8kgf MIN

2.7 使用寿命: 10000次

2.8 工作温度: -30℃~+80℃



RECOMMENDED P.C.B. LAYOUT
TOLERANCE UNSPECIFIED ±0.05mm

A1	GND	B12	GND
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	DP1	B7	DN2
A7	DN1	B6	DP2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A12	GND	B1	GND
PIN	SIGNAL NAME	PIN	SIGNAL NAME

产品图

PRODUCT CHART DWG

公差一览表

TOLERANCE UNLESS OTHERWISE

X.	±0.35	X.	±5.°
.X	±0.25	.X	±2.°
.XX	±0.20	.XX	±1.°
.XXX	±0.05	.XXX	±0.5°

深圳市精拓金电子有限公司
Shenzhen Jing Tuo Jin Electronics Co., Ltd.

单位 UNITS	MM	制图 DRAWING	L-S-S	产品料号 PRODUCT PART NO.	918-418K2024S40028
比例 SCALE	1:1	审核 CHKD	G-Z-F	产品名称 PRODUCT NO.	USB TYPE C 16P 沉板1.2mm 3A
日期 DATE	2021-03-10	核准 APPD	黄国荣	角法 VIEW	版本 VER



版本
VER

A0