

NOTES:

1. ELECTRICAL SPECIFICATIONS:

CURRENT RATING: 0.5A.

VOLTAGE RATING: 5V.

CONTACT RESISTANCE: 50 MILL. OHM MAX.

INSULATION RESISTANCE: 1000 MEG. OHM MIN.


2. MECHANICAL SPECIFICATIONS:

DURABILITY: 5000 CYCLES MIN.

GENERAL TOLERANCE		DWG NO.			APPD:		Scale	1:1
X.±0.45	x.±5°	Title	1.45H,MICRO SIM CARD CONNECTOR		CHKD:		UNIT	mm
.X±0.35	.x.±2°				DR:			
.XX±0.25	.xx.±1°	Part NO.	5001B-SIM145-129		Date:	2021/06/11		
.XXX±0.15	.xxx.±0.5°							
SHEET	1/2							

东莞市文章济美电子有限公司

〈图一〉




〈表一〉


包装数量

PCS/卷	卷/箱	PCS/箱
1500	11	16500

〈图二〉



〈图三〉



NOTE:

1. 依〈图一〉示放置产品于下载中, 每穴放置1PCS产品.
2. 包装机包好后, 在REEL的个等分点贴上胶带, 以防止REEL张开, 每REEL贴1PCS标签, 如〈图二〉示
3. 包装数量见如〈表一〉示
4. 包装成箱见如〈图三〉示
箱底放保丽龙板, 再依次将指定数量的卷装产品放入箱内,
四角分别放入四个三角护板, 最上层再放上保丽龙板.
5. 封箱, 在封好的纸箱上按客户要求写上料号, 数量等
6. 适用成品料号见如下〈表二〉

GENERAL TOLERANCE		图号			设计	1:1
X.±0.45	.x.±5°	品名	1. 45H, MICRO SIM CARD		审核	单位 mm
.X±0.35	.x.±2°		包装图		核准	视 角
.XX±0.25	.xx.±1°	料号	5001B-SIM145-129		日期	2021/06/11
XXX±0.15	.xxx.±0.5°	页号	2/2		版本	A0

东莞市文章济美电子有限公司