






REV.	ECN NO.	DESCRIPTION	DATE	DESIGN



NOTES:


- 1.BASE: PA66
- 2.PIN: Brass
- 3.Solder Tab: Brass

SPECIFICATIONS:

- 1.Spacing: 1.25
- 2.Voltage Rating : 125V AC DC
- 3.Current Rating: 1A AC DC
- 4.Insulation Resistance: 100MΩ Min
- 5.Contact Resistance: 20mΩ Max
- 6.Withstanding voltage: 500V AC 1/Minute
- 7.Temperatuer Range: -25℃ ~+ 85℃

PIN number variable size comparison table

PART NO	PIN	A	B	C	D
JXT-MX1.25-2PWZ	2	1.25	4.40	3.20	
JXT-MX1.25-3PWZ	3	2.50	5.65	4.45	
JXT-MX1.25-4PWZ	4	3.75	6.90	5.70	2.50
JXT-MX1.25-5PWZ	5	5.00	8.15	6.95	3.75
JXT-MX1.25-6PWZ	6	6.25	9.40	8.20	5.00
.....					
JXT-MX1.25-16PWZ	16	18.75	21.90	20.70	17.50



TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
.X±0.30	X.* ±5°	PART NO.	TITLE:		
.XX±0.20	X.X* ±1°	JXT-MX1.25-NPWZ	WAFER 1.25 间距		
.XXX±0.10	X.XX* ±0.5°	DESIGN: Ethan	MANUFACTURE DWG		
UNITS	mm	CHED: Olvia			
MATERILA	— — —	APPD: Ava			
FINISH	— — —		SCALE	SHEET	
			N:A	1/1	