





CAD FILE:

DATE 日期	VER 版本	CHANGE HISTORY 变更历史	DRAWING 變更者
2013-08-10	A		G.M.Chen
2024-12-29	B	调整开口尺寸 	G.M.Chen



SPECIFICATIONS

- 1、Current Rating: 1A AC, DC
- 2、Voltage Rating: 125V AC, DC
- 3、Temperature Range: -25℃~+85℃
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 100MΩ Min
- 6、Withstanding Voltage: 500V AC/minute
- 7、Material: Phosphoric bronze Tin-plated
- 8、Applicable Wire Sizes: AWG#28~32#



APPROVALS			DATE	DEALON德之隆® ELECTRONICS CO.,LTD		
DRAWN	G.M.Chen	2013-08-10				
CHECKED	Leo Li		TITLE:	1.25mm Crimp Style Connectors		
APPROVALS	Scot.Chen		PART NO.	X1251-T-PN		
TOLERANCES ARE	30~以上	±0.30	ANGLE	UNIT: mm	SCALE: 1:1	SHEET 1 OF 1
	10~30	±0.20		DRAWING NO.		PROJ. 
	5~10	±0.15				
	~ 5	±0.15				
		±2'				

	A		NEW			
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO