




REV.	ECN.NO.	MODIFY.CONTENT	DATE
A		NEW	2015/10/31

NOTE:

1. ELECTRICAL CHARACTERISTICS
  - 1-1. CONTACT RESISTANCE: 80 milliohms MAX.
  - 1-2. INSULATION RESISTANCE: 1,000 Megohms MIN.
  - 1-3. DIELECTRIC WITHSTANDING VOLTAGE: 500V AC MIN FOR 1 MINUTE.
2. MECHANICAL CHARACTERISTICS
  - 2-1. RETENTION FORCE:MIN.100gf/PIN
  - 2-2. DURABILITY: 5,000 CYCLES
  - 2-3. PRODUCT COMPLIED WITH ROHS



P8	DAT1
P7	DATO
P6	VSS
P5	CLK
P4	VDD
P3	CMD
P2	CD/DAT3
P1	DAT2
PIN NUMBER	SIGNAL NAME

3	SHELL	1	STAINLESS STEEL	
2	CONTACT	8	COPPER ALLOY MATING AREA Au PLATED	
1	HOUSING	1	THERMOPLASTIC UL94V-0,BLACK	
ITEM	MANE	Q'TY/EACH	MATERIAL/FINISHED	REMARK

GENERAL TOLERANCE		DWG NO.			APPD:	WIND	Scale	1:1
X.±0.45	x.±5°	Title	1.5H 8PIN TF CARD 简易式 无柱		CHKD:		UNIT	mm
.X±0.35	.x.±2°				DR:			
.XX±0.25	.xx.±1°	Part NO.	5001B-TF150-055		Date	2015/10/31		
.XXX±0.15	.xxx.±0.5°							
SHEET	1/1							

东莞市文章济美电子有限公司