






PIN number variable size comparison table				
PART NO	PIN	A	B	C
JXT-HY2.0-2PZZ	2	2.00	6.00	2.50
JXT-HY2.0-3PZZ	3	4.00	8.00	2.50
JXT-HY2.0-4PZZ	4	6.00	10.00	3.50
JXT-HY2.0-5PZZ	5	8.00	12.00	5.50
JXT-HY2.0-6PZZ	6	10.00	14.00	7.50
JXT-HY2.0-7PZZ	7	12.00	16.00	9.50
.....				
JXT-HY2.0-15PZZ	15	28.00	32.00	15.50



10. 铅和镉等六大有害物质含量要符合环保要求。

2	端子 Contact	黄铜	N*1	电镀(锡):整个表面镀底镍 30u"MIN,再镀锡 80u"MIN	TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
					.X±0.30	X.* ±5°	PART NO. JXT-HY2.0-NPZZ	TITLE: HY2.0MM 直针带扣		
					.XX±0.20	X.X* ±1°				
1	基座 Wafer	LCP (UL94V-0)	1	白色	.XXX±0.10	X.XX*±0.5°	DESIGN: Ethan	MANUFACTURE DWG		
					UNITS	mm				
					MATERILA	— — —				
序号	名称	材料	数量	备注	FINISH	— — —	APPD: Ava		SCALE N:A	SHEET 1/1