






MATERIAL:

1. Insulator: PBT+30% Glass Fiber
2. Contact: Brass
3. Contact Plated: Gold Flash over Tin Or Gold Plated Or Tin Plated
4. Shell: Steel, Nickel Plated

SPECIFICATION:

1. Current Rating: 5 AMPS
2. Insulation Resistance: 100M Ω MIN. At 500VDC
3. Dielectric Strength: 500V for One minute
4. Operation Temperature: -55° C~+105° C.

*【胶芯颜色、防火要求、环保要求及电镀规格 依据客户实际订单要求为准】



RECOMMEND PCB LAYOUT (T=1.6)

PCB TOLERANCE: ±0.05

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED		APR.	TITLE: DP9F 插板静触头插座		
.X±0.35	X.*±5°	Alex	DWG NO. XY-DMS-9PSM		
.XX±0.25	.X.*±3°	Jack	PROJ.  CUSTOMER DRAWING		
.XXX±0.15	.XX.*±1°	Can	SIZE A4	SCALE 1:1	SHEET 1/1 REV. A