




SPECIFICATIONS

Current Rating: 1.5 Amps
Insulation Resistance: 1000M Ω Min
Contact Resistance: 20m Ω Max
Withstanding Voltage: AC 500V
Operation Temperature: -40°to+105°
Contact Material: Brass
Standard: PA6T
Insulator Material: Polyester(UL 94V-0)
Contact Plating: Gold Flash
Max.Processing Temp: 240°C for 30-60seconds
(260°C for 5 seconds)



RECOMMEND P.C.B LAYOUT
PCB TOLERANCE:±0.05 (TOP VIEW)

P/N	PIN	DIM.A	DIM.B
XY-PM200-1-01P-Z-4.3	1	0.00	2.00
XY-PM200-1-02P-Z-4.3	2	2.00	4.00
XY-PM200-1-03P-Z-4.3	3	4.00	6.00
XY-PM200-1-04P-Z-4.3	4	6.00	8.00
XY-PM200-1-05P-Z-4.3	5	8.00	10.00
XY-PM200-1-06P-Z-4.3	6	10.00	12.00
XY-PM200-1-07P-Z-4.3	7	12.00	14.00
XY-PM200-1-08P-Z-4.3	8	14.00	16.00
XY-PM200-1-09P-Z-4.3	9	16.00	18.00
.....			
XY-PM200-1-40P-Z-4.3	40	(PIN-1)x2.0	(PIN)x2.0

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd				
TOLERANCE UNLESS OTHERWISE SPECIFIED						
.X±0.3	X.*± 5°	APR.	Alex	TITLE: 2.0FH H4.3 1xnPin 180 W2.4 U PC2.8 6T		
.XX±0.2	.X*± 1	CHK.	Jack	DWG NO. PM2.00-1-NP-Z		
.XXX±0.1	.XX*± 0.5	DRA.	Can	PROJ. 		CUSTOMER DRAWING
				SIZE A4	SCALE 1:1	SHEET 1/1