

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.

REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL	24FEB2023	QY	CW
	A1	ECR-23-185132	11OCT2023	QY	CW
	B	ECR-25-257311	19SEP2025	QY	GY

注释：







1. 技术参数：
额定电压：1000V/400V/25V
额定电流：70A/20A/5A
过电压等级：3
污染等级：3
插拔次数：500次
接线范围：70A 10-12 mm²/7AWG
20A 2.5-4 mm²/14AWG-12AWG
5A 0.5-0.75 mm²/20AWG-18AWG
(端子螺丝单独订购
5 A:T2210002010000
20A:T2220002040000
70A:T2240002120000)

MATING INTERFACE PANEL
RECOMMENDED DISTANCE

配合界面推荐面板间距离





SCALE 3:5



SCALE 3:5

T2100182201-000	BPSC-12/2/4-F	BPSC-12/2/4 FEMLE INSERT BPSC-12/2/4 母插
PART NUMBER 料号	PART DESCRIPTION 描述	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 24FEB2023 QIANG YUAN	 TE Connectivity		
		CHK 24FEB2023 GINO YAO			
		APVD 24FEB2023 CHRIS WANG			
		PRODUCT SPEC 108-137664			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:	NAME BPSC-12/2/4-F		
		0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±	SIZE A3		
MATERIAL -		FINISH -	CAGE CODE 00779		
			DRAWING NO T2100182201000		
			RESTRICTED TO -		
			SCALE 1:1		
			SHEET 1 OF 1		
			REV B		



RECOMMENDED PANEL CUT OFF DIMENSION
SUPPLEMENTARY INSULATION PROVIDED BY EQUIPMENT
推荐面板开孔尺寸，附加绝缘由整机提供