






- MATERIAL:

1. Insulator: PBT+30% Glass Fiber
2. Contact: Brass
3. Contact Plated: Gold Flash over Tin Or Gold Plated Or Tin Plated
4. Shell: Steel, Nickel Plated

- SPECIFICATION:

1. Current Rating: 3 AMPS
2. Insulation Resistance: 100M Ω MIN. At 500VDC
3. Dielectric Strength: 500V for One minute
4. Operation Temperature: -55° C~+105° C.

※【胶壳颜色、防火要求、环保要求及电镀规格 依客户实际订单要求为准】



RECOMMEND PCB LAYOUT (T=1.6)
PCB TOLERANCE: ±0.05

DIMENSION IN mm		厦门市辛译精密电子有限公司			
TOLERANCE UNLESS OTHERWISE SPECIFIED		Xiamen XinYi Xyeconn Electronics Co.,Ltd			
.X±0.35	X.*± 5°	APR.	Alex	TITLE: DR9MX#	
.XX±0.25	.X.*± 3°	CHK.	Jack	DWG NO. XY-DMR-9PCG	
.XXX±0.15	.XX.*± 1°			PROJ.	
		DRA.	Can	SIZE A4	SCALE 1:1
				SHEET 1/1	REV. A