





MATERIAL:

1. Insulator: PBT+30% Glass Fiber
2. Contact: Brass
3. Contact Plated: Gold Flash over Tin Or Gold Plated Or Tin Plated
4. Shell: Steel, Nickel Plated

SPECIFICATION:

1. Current Rating: 3 AMPS
2. Insulation Resistance: 100M Ω MIN. At 500VDC
3. Dielectric Strength: 500V for One minute
4. Operation Temperature: -55 $^{\circ}$ C ~ +105 $^{\circ}$ C.

* 【胶芯颜色、防火要求、环保要求及电镀规格 依据客户实际订单要求为准】

RECOMMEND PCB LAYOUT (T=1.6)
PCB TOLERANCE: ±0.05

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED		APR.	Alex	TITLE: DR25FX	
.X±0.35	.X*±5°	CHK.	Jack	DWG NO. XY-DMR-25PCM	
.XX±0.25	.X*±3°	PROJ.	Can	CUSTOMER DRAWING	
.XXX±0.15	.XX*±1°	SIZE	A4	SCALE	1:1
		SHEET	1/1	REV.	A