





REV.	Q'TY	ECN. NO.	APR.	DATE

SPECIFICATIONS

Current Rating: 3Amps
 Insulation Resistance: 1000MΩ Min
 Contact Resistance: 20mΩ Max
 Withstanding Voltage: AC 1000V
 Operation Temperature: -40°to+105°
 Contact Material: Brass
 Standard: PA6T
 Insulator Material: Polyester(UL 94V-0)
 Contact Plating: Gold Flash
 Max.Processing Temp: 240°C for30-60seconds
 (260°C for5seconds)

P/N	PIN	DIM.A	DIM.B
PM2.54-2-01P-S	2*1	0.00	2.54
PM2.54-2-02P-S	2*2	2.54	5.08
PM2.54-2-03P-S	2*3	5.08	7.62
PM2.54-2-04P-S	2*4	7.62	10.16
PM2.54-2-05P-S	2*5	10.16	12.70
PM2.54-2-06P-S	2*6	12.70	15.24
PM2.54-2-07P-S	2*7	15.24	17.78
PM2.54-2-08P-S	2*8	17.78	20.32
PM2.54-2-09P-S	2*9	20.32	22.86
.....
PM2.54-2-40P-S	2*40	(PIN-1)X2.54	(PIN)X2.54



DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyconn Electronics Co.,Ltd		
TOLERANCE UNLESS OTHERWISE SPECIFIED		APR.	Alex	TITLE: 2.0FH H6.35 2xnPi2.54FH H8.5 2xnPin SMT U型 PC7.2 PBB.8 6Tn 180μ Y# PC2.8 6T
.X±0.3	X.*± 5°	CHK.	Jack	DWG NO. PM2.54-2-NP-S
.XX±0.2	.X*± 1	DRA.	Can	PROJ. CUSTOMER DRAWING
.XXX±0.1	.XX*± 0.5	SIZE	A4	SCALE 1:1 SHEET 1/1 REV. A