



REV.	Q'TY	ECN. NO.	APR.	DATE



- SPECIFICATIONS**
- CURRENT RATING: 0.3A .
  - VOLTAGE RATING 30V AC/DC.
  - TEMPERATURE RANGE: -35°C TO +85°C
  - CONTACT RESISTANCE: 90mΩ MAX.
  - INSULATION RESISTANCE: 50 MΩ MIN.
  - WITHSTANDING VOLTAGE: 100V AC/MINUTE.



PIN	A	B	C
XY-10DP-DF40C	3.52	1.6	1.0
XY-12DP-DF40C	3.92	2.0	
XY-20DP-DF40C	5.52	3.6	
XY-24DP-DF40C	6.32	4.4	1.2
XY-30DP-DF40C	7.52	5.6	1.5
XY-34DP-DF40C	8.32	6.4	2.3
XY-40DP-DF40C	9.52	7.6	3.2
XY-44DP-DF40C	10.32	8.4	
XY-50DP-DF40C	11.52	9.6	
XY-60DP-DF40C	13.52	11.6	
XY-70DP-DF40C	15.52	13.6	
XY-80DP-DF40C	17.52	15.6	
XY-90DP-DF40C	19.52	17.6	
XY-100DP-DF40C	21.52	19.6	

The product is high	H
XY-XDP-DF40C	1.45
XY-XDP-DF420C	1.95
XY-XDP-DF424C	2.40
XY-XDP-DF429C	2.90
XY-XDP-DF434C	3.40
XY-XDP-DF439C	3.90

DIMENSION IN mm		<p><b>厦门市辛译精密电子有限公司</b> Xiamen XinYi Xyconn Electronics Co.,Ltd</p>	
TOLERANCE UNLESS OTHERWISE SPECIFIED			
.X±0.5	.X*± 2	APR. Alex	TITLE: 0.40MM BTB PLUG
.XX±0.35	.X*± 1	CHK. Jack	DWG NO. XY-NDS-DF429C
.XXX±0.25	.XX*±	DRA. Can	PROJ.  CUSTOMER DRAWING
SIZE A4	SCALE 1:1	SHEET 1/1	REV. A