


MATERIAL:

- 1.Insulator:PBT+30%Glass Fiber
- 2.Contact:Brass
- 3.Contact Plated:Gold Flash over Tin Or
Glod Plated Or Tin Plated
- 4.Shell:Steel,Nickel Plated

SPECIFICATION:

- 1.Current Rating:3 AMPS
- 2.Insulation Resistance: 100M Ω MIN. At 500VDC
- 3.Dielectric Strength: 500V for One minute
- 4.Operation Temperature: -55° C~+105° C.

※【胶芯颜色、防火要求、环保要求及电镀规格 依据客户实际订单要求为准】



RECOMMEND PCB LAYOUT (T=1.6)

PCB TOLERANCE:±0.05

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED					
.X±0.35	X.*± 5°	APR.	Alex	TITLE: DP-9M 9.6mm	
.XX±0.25	.X.*± 3°	CHK.	Jack	DWG NO. XY-DMS-9PSG	
.XXX±0.15	.XX.*± 1°	DRA.	Can	PROJ.	CUSTOMER DRAWING
		SIZE	A4	SCALE	1:1
		SHEET	1/1	REV.	A